

Philips
Micro Hi-Fi System



MC127

Relax with great music

Obsessed with sound

Tune in to superb sound from a surprisingly compact and sleek design. The MC127 Micro Hi-Fi System will enhance your living space while enriching your music listening experience. Just press Play to enjoy room-filling, dynamic bass sounds.

Enrich your sound experience

- Dynamic Bass Boost for deep and dramatic sound
- Play CD, CD-R and CD-RW discs
- MP3 Link for portable music playback

Easy to use

- Digital tuning with 20 pre-set stations for extra convenience

Fits any space, any lifestyle

- Compact design
- Easy-to-use remote control included

PHILIPS

Specifications

Sound

- Output Power: 2 x 2 W RMS/2 x 4 W music power
- Volume Control: Volume Control up/down
- Sound Enhancement: Dynamic Bass Boost

Loudspeakers

- Main Speaker: 3" woofer

Audio Playback

- Playback Media: CD, CD-R, CD-RW
- Disc Playback Modes: 20-Track Programmable, Repeat/one/all/programme
- Loader Type: Top

Tuner/Reception/Transmission

- Tuner Bands: FM Stereo
- Station presets: 20

Connectivity

- Other connections: FM fixed pigtail antenna
- Audio Connections: 3.5 mm Line in

Convenience

- Loader type: top

Accessories

- Included accessories: IFU/User Manual, World Wide Warranty leaflet, MP3 Line-in cable
- Remote control: 15-key remote control

Dimensions

- Set dimensions (W x H x D): 152 x 175 x 250 mm
- Main speaker dimensions (W x H x D): 132 x 175 x 158 mm
- Packaging dimensions (W x H x D): 480 x 220 x 238 mm
- Weight incl. Packaging: 3.8 kg

Highlights

Dynamic Bass Boost

Dynamic Bass Boost maximises your music enjoyment by emphasising the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.



Issue date 2013-05-29

Version: 2.1.8

12 NC: 8670 000 79891
EAN: 87 12581 61305 1

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com