



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PS6020

20-outlet Vertical Power Strip with 15-ft. Cord

Highlights

- 20 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15-ft. cord
- 60" length



Description

Tripp Lite's PS6020 power strip offers 15 amp, 120V multi-outlet AC power distribution in a convenient 60 inch mountable housing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications. Includes 20 NEMA 5-15R output receptacles with 2.795 inch center-to-center spacing, 15 ft AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 20 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: 60 in. corded, mountable power strip

Applications

- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications

Package Includes

- PS6020
- Mounting hardware
- Instruction manual

Features

- Sturdy all-metal 60 inch corded strip format with 2.795 inch center-to-center outlet spacing
- Included mounting hardware
- Includes 20 NEMA 5-15R output receptacles
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz

Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	20 Nema 5-15R
Outlet spacing	2.795 in.
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	Nema 5-15P
Input plug features	Black
Input cord length (ft.)	15
Input cord length (m)	4.572
Input cord gauge, type	14/3 SJT
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Lighted 2 position switch controls power to all outlets
Locking switch cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Unit Dimensions (HWD/in)	60 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	152.4 x 3.8 x 3.8
Unit weight (lbs)	5.0
Unit weight (kg)	2.27
Material of construction	Aluminum
Mounting accessories included	Includes mounting clips
Receptacle Color	Black
AC line cord color	Black
Style	Bench/Cabinet Mount
Form factors supported	Supports horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
Outlets center to center measurement	69mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=195.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.