

3 ft Mini DisplayPort™ to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

StarTech ID: MDP2VGAMM3W



The MDP2VGAMM3W active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped desktop or laptop directly to a nearby VGA monitor or projector, saving the expense of additional adapters while eliminating the clutter of excess cable. The converter features a stylish white design, that is well-suited for connecting Mac® computers.

The adapter cable is compatible with Intel® Thunderbolt Monday, September 30, 2013 8:42:43 PMrade;, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM3W is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal

Technical Specifications

Warranty	2 Years
Chipset ID	ANALOGIX 9832
Converter Type	Active
USB Pass-Through	No
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Maximum Analog Resolutions	1920x1200 / 1080p (Output)
Maximum Cable Length	915 mm [36 in]
Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Cable Length	930 mm [36.6 in]
Color	Black
Product Height	15 mm [0.6 in]
Product Length	930 mm [36.6 in]
Product Weight	78 g [2.8 oz]
Product Width	34 mm [1.3 in]
Humidity	40%-85%RH
Operating Temperature	0°C to 60°C (32°F to 140°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Shipping (Package) Weight	0.1 kg [0.2 lb]
Included in Package	Mini DisplayPort to VGA Adapter Cable

Certifications, Reports and Compatibility

