



Joker Ratchet Wrench Set



Design: Hexagon bolt heads or nuts

Application: Foot-and-ratchet wrench, hold function by metal plate in his mouth, reduces the risk of losing screws and nuts; replaceable metal plate in his mouth secures with extra hard teeth nuts and bolts and reduces the risk of slipping; integrated end stop can prevent slipping from the screw head down and allows the application of high torque, the twin hexagonal geometry ensures the positive connection with screw or nut and thus reducing the risk of slipping; backward tilt angle of only 30 ° on the side of the mouth to avoid the time-consuming turning of the key in the screw; ratchet mechanism on the ring side with exceptionally high fine teeth of 80 teeth for flexibility in confined spaces, special forged geometry for high torque transmission and high bending stiffness; powerful chrome-molybdenum steel, nickel-chrome plating for high corrosion protection.

 Code	
05020011001	Joker 1 x 8x144; 1 x 10x159; 1 x 11x165; 1 x 12x170,7; 1 x 14x188; 1 x 15x200; 1 x 16x212; 1 x 18x235 1