



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: INTERNETOFFICE300

### Internet Office 300VA Ultra-compact Standby 120V UPS

#### Highlights

- 300VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets



#### Description

Tripp Lite's INTERNETOFFICE300 UPS System provides complete power protection for your entire computer set-up. 300 VA power capacity maintains your Internet connection allowing you to work online through short blackouts or safely shut down during longer ones. Unique design features 6 outlets (3 UPS & surge + 3 surge-only outlets) and diagnostic LEDs. Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment. A 6-ft. telephone cord is also included. \$100,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only) covers connected equipment.

#### Package Includes

- INTERNETOFFICE300 UPS System
- Phone cable
- Instruction manual

#### Features

- 300 VA output power rating (150 watts)
- Up to 11 minutes backup time (single PC; 15-in monitor)
- Battery run time: 10 minutes half load/4 minutes full load
- 6 protected outlets (3 UPS & surge + 3 surge-only outlets); 6-ft. cord
- Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment; 6-ft. telephone cord included
- Complete surge protection and EMI/RFI noise filtering
- \$100,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico, & Canada Only) covers connected equipment
- 5 diagnostic LEDs indicate AC present, line fault, on battery, overload and battery low/replace

#### Specifications

| OUTPUT                        |     |
|-------------------------------|-----|
| Output Volt Amp Capacity (VA) | 300 |
| Output Watt Capacity (watts)  | 150 |

|  |  |
|--|--|
| Nominal Output Voltage(s) Supported      | 120V   |
| Frequency compatibility                  | 50 / 60 Hz   |
| Output voltage regulation (Battery mode) | +/- 5%   |
| Built-in UPS output receptacles          | 6 5-15R outlet(s)                                    |
| Surge suppression only outlets           | 3 UPS outlets, 3 surge-only outlets                  |
| Output circuit breaker                   | 15A  |
| Output AC waveform (AC mode)             | Sine wave  |
| Output AC waveform (battery mode)        | PWM sine wave  |
| <b>INPUT</b>                             |  |
| Rated input current (at maximum load)    | 12A  |
| Nominal Input Voltage(s) Supported       | 120V AC  |
| UPS input connection type                | 5-15P  |
| UPS Input cord length (ft.)              | 6  |
| UPS Input cord length (m)                | 1.8  |
| Recommended Electrical Service           | 15A 120V   |
| Input cord length (ft.)                  | 6  |
| Input cord length (m)                    | 1.8  |
| <b>BATTERY</b>                           |  |
| Full load runtime (minutes)              | 4 min. (150w)  |
| Half load runtime (minutes)              | 10 min. (75w)  |
| DC system voltage (VDC)                  | 12   |
| <b>LEDS ALARMS &amp; SWITCHES</b>        |  |
| LED Indicators                           | 5 LEDs indicate complete UPS operational status      |
| Switches                                 | Power off / on switch                                |
| <b>SURGE / NOISE SUPPRESSION</b>         |  |
| UPS AC suppression joule rating          | 380  |
| UPS AC suppression response time         | Instantaneous  |
| UPS Dataline suppression                 | 1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet |
| EMI / RFI AC noise suppression           | Yes  |
| AC suppression joule rating              | 380  |

|  |  |
|--|--|
| AC suppression response time   | Instantaneous  |
| Dataline suppression   | 1 line TEL / DSL or 10Base T Ethernet protection           |
| <b>PHYSICAL</b>  |  |
| Installation form factors supported with included accessories                          | Tower; Ultra-compact desktop                               |
| Primary form factor  | Desktop  |
| UPS / Power Module dimensions in primary form factor (height x width x depth / inches) | 2.6 x 11 x 4.5   |
| UPS / Power Module dimensions in primary form factor (height x width x depth / cm)     | 6.7 x 27.9 x 11.4  |
| UPS / Power Module weight (lbs)  | 4  |
| UPS / Power Module weight (kg)   | 1.8  |
| UPS Shipping dimensions (height x width x depth / inches)                              | 4.5 x 13 x 8.2   |
| UPS Shipping dimensions (height x width x depth / cm)                                  | 11.4 x 33 x 21   |
| Shipping weight (lbs)  | 5.4  |
| Shipping weight (kg)   | 2.5  |
| UPS housing material   | ABS  |
| <b>ENVIRONMENTAL</b>   |  |
| Operating Temperature Range  | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius  |
| Storage Temperature Range  | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity  | 0 to 95%, non-condensing                                   |
| AC mode BTU / hr. (full load)  | 32.6   |
| Battery mode BTU / hr. (full load)   | 44.3   |
| <b>LINE / BATTERY TRANSFER</b>   |  |
| Transfer time  | 2-4 milliseconds   |
| Low voltage transfer to battery power (setpoint)                                       | 99V  |
| High voltage transfer to battery power (setpoint)                                      | 141V   |
| <b>SPECIAL FEATURES</b>  |  |
| Green & high efficiency features   | Greater than 95% efficiency - GREEN UPS                    |
| <b>CERTIFICATIONS</b>  |  |

|   |  |
|---|--|
| <b>UPS Certifications</b>   | Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI) |
| <b>WARRANTY</b>   |  |
| <b>Product Warranty Period (U.S. &amp; Canada)</b>                    | 3-year limited warranty  |
| <b>Product Warranty Period (International)</b>                        | 2-year limited warranty  |
| <b>Product Warranty Period (Mexico)</b>                               | 3-year limited warranty  |
| <b>Product Warranty Period (Puerto Rico)</b>                          | 3-year limited warranty  |
| <b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b> | \$100,000 <a href="#">Ultimate Lifetime Insurance</a>  |

## Related Items

### Optional Products

| Related Model                  | Description  | Qty. |
|--------------------------------|--|------|
| <a href="#">WEXT5-INTERNET</a> | 5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems | 1    |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=9](http://www.tripplite.com/en/products/model.cfm?txtModelID=9).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.