Safety warnings

Keep your phone away from small children and

Keep your phone and all accessories out of the reach of small children or animals. Small parts may cause choking or serious injury if swallowed.

Protect your hearing



Excessive exposure to sound at high volumes can cause hearing damage. Always turn the volume down before plugging the earphones into an audio source and use only the minimum volume setting necessary to hear your conversation or music.

Install mobile phones and equipment with caution

Ensure that any mobile phones or related equipment installed in your vehicle are securely mounted. Avoid placing your phone and accessories near or in an air bag deployment area. Improperly installed wireless equipment can cause serious injury when air bags inflate rapidly.

Handle and dispose of batteries and chargers

- Use only Samsung-approved batteries and chargers specifically designed for your phone. Incompatible batteries and chargers can cause serious injuries or damage to your phone.
- · Never dispose of batteries or phones in a fire. Follow all local regulations when disposing of used batteries
- · Never place batteries or phones on or in heating devices, such as microwave ovens, stoves, or radiators. Batteries may explode when overheated.
- · Never crush or puncture the battery. Avoid exposing the battery to high external pressure, which can lead to an internal short circuit and overheating.

Avoid interference with pacemakers

Maintain a minimum of 15 cm (6 inches) between mobile phones and pacemakers to avoid potential interference, as recommended by manufacturers and the independent research group, Wireless Technology Research. If you have any reason to suspect that your phone is interfering with a pacemaker or other medical device, turn off the phone immediately and contact the manufacturer of the pacemaker or medical device for guidance.

Turn off the phone in potentially explosive environments

Do not use your phone at refuelling points (service stations) or near fuels or chemicals. Turn off your phone whenever directed by warning signs or instructions Your phone could cause explosions or fire in and around fuel or chemical storage and transfer areas or blasting areas. Do not store or carry flammable liquids, gases or explosive materials in the same compartment as the phone, its parts, or accessories.

Reduce the risk of repetitive motion injuries

While using your phone, hold the phone with a relaxed grip, press the keys lightly, use special features that reduce the number of keys you have to press (such as templates and predictive text), and take frequent breaks

Do not use the phone if the screen is cracked or broken

Broken glass or acrylic could cause injury to your hand and face. Bring the phone to a Samsung service centre to replace the screen. Damage caused by careless handling will void your manufacturer's warranty.

C€0168

www.samsungmobile.com

Some of the contents in this manual may differ from your

phone depending on the software of the phone or your service

Mobile Phone

user manual

Printed in Korea Code No.:GH68-26836A English (EU). 11/2010. Rev. 1.2



Safety precautions

Drive safely at all times

Avoid using your phone while driving and obey all regulations that restrict the use of mobile phones while driving. Use hands-free accessories to increase your safety when possible

Follow all safety warnings and regulations

Comply with any regulations that restrict the use of a mobile phone in a certain area

Use only Samsung-approved accessories

Using incompatible accessories may damage your phone or cause injury.

Turn off the phone near medical equipment

Your phone can interfere with medical equipment in hospitals or health care facilities. Follow all regulations, posted warnings, and directions from medical

Turn off the phone or disable the wireless functions when in an aircraft

Your phone can cause interference with aircraft equipment. Follow all airline regulations and turn off your phone or switch to a mode that disables the wireless functions when directed by airline personnel.

Protect batteries and chargers from damage

- · Avoid exposing batteries to very cold or very hot temperatures (below 0° C/32° F or above 45° C/ 113° F). Extreme temperatures can reduce the charging capacity and life of your batteries
- · Prevent batteries from contacting metal objects, as this can create a connection between the + and - terminals of your batteries and lead to temporary or permanent battery damage
- Never use a damaged charger or battery.

Handle your phone carefully and sensibly

- · Do not disassemble your phone due to a risk of electric
- Do not allow your phone to get wet—liquids can cause serious damage and will change the color of the label that indicates water damage inside the phone. Do not handle your phone with wet hands. Water damage to your phone can void your manufacturer's warranty.

- · Avoid using or storing your phone in dusty, dirty areas to prevent damage to moving parts.
- Your phone is a complex electronic device—protect it from impacts and rough handling to avoid serious
- Do not paint your phone, as paint can clog moving parts and prevent proper operation.
- If your phone has a camera flash or light, avoid using it close to the eyes of children or animals.
- Your phone may be damaged by exposure to magnetic fields. Do not use carrying cases or accessories with magnetic closures or allow your phone to come in contact with magnetic fields for extended periods of

Avoid interference with other electronic devices Your phone emits radio frequency (RF) signals that


may interfere with unshielded or improperly shielded electronic equipment, such as pacemakers, hearing aids, medical devices, and other electronic devices in homes or vehicles. Consult the manufacturers of your electronic devices to solve any interference problems you experience.



Important usage information

Use your phone in the normal position

Avoid contact with your phone's internal antenna



Allow only qualified personnel to service your phone

Allowing unqualified personnel to service your phone may result in damage to your phone and will void your

Ensure maximum battery and charger life

- Avoid charging batteries for more than a week, as overcharging may shorten battery life.
- · Over time, unused batteries will discharge and must be recharged before use.
- · Disconnect chargers from power sources when not in use.
- · Use batteries only for their intended purpose

Handle SIM cards with care

- · Do not remove a card while the phone is transferring or accessing information, as this could result in loss of data and/or damage to the card or phone.
- · Protect cards from strong shocks, static electricity, and electrical noise from other devices.
- Do not touch gold-coloured contacts or terminals with your fingers or metal objects. If dirty, wipe the card with a soft cloth.

Ensure access to emergency services

Emergency calls from your phone may not be possible in some areas or circumstances. Before travelling in remote or undeveloped areas, plan an alternate method of contacting emergency services personnel.

Specific Absorption Rate (SAR) certification

Your phone conforms to European Union (EU) standards that limit human exposure to radio frequency (RF) energy emitted by radio and telecommunications equipment. These standards prevent the sale of mobile phones that exceed a maximum exposure level (known as the Specific Absorption Rate, or SAR) of 2.0 W/kg. During testing, the maximum SAR recorded for this model was 0.720 W/kg. In normal use, the actual SAR is likely to be much lower, as the phone has been designed to emit only the RF energy necessary to transmit a signal to the nearest base station. By automatically emitting lower levels when possible, your phone reduces your overall exposure to RF energy. The Declaration of Conformity of this manual demonstrates your phones compliance with the European Radio & Terminal Telecommunications Equipment (R&TTE) directive. For more information about the SAR and related EU standards, visit the Samsung mobile phone website

Correct disposal of this product

(Waste Electrical & Electronic Equipment)

(Applicable in the European Union and other European countries with separate collection systems) This marking on the product, accessories

or literature indicates that the product and its electronic accessories (e.g. charger, headset, USB cable) should not be disposed of with other household waste at the end of their working life. To prevent possible harm to the environment or human health from uncontrolled waste disposal, please separate these items from other types of waste and recycle them responsibly to promote the sustainable reuse of material

Household users should contact either the retailer where they purchased this product, or their local government office, for details of where and how they can take these items for environmentally safe recycling

Business users should contact their supplier and check the terms and conditions of the purchase contract. This product and its electronic accessories should not be mixed with other commercial wastes for disposal

This EEE is compliant with RoHS


Correct disposal of batteries in this product

(Applicable in the European Union and other European countries with separate battery return systems)

This marking on the battery, manual or packaging indicates that the batteries in this product should not be disposed of with other household waste at the end of their working life. Where marked, the chemical symbols Hg, Cd or Pb indicate that the battery contains mercury, cadmium or lead above the reference levels in EC Directive 2006/66. If batteries are not properly disposed of, these substances can cause harm to human health or the environment.

To protect natural resources and to promote material reuse, please separate batteries from other types of waste and recycle them through your local, free battery





4-way navigation key In Idle mode, access use defined menus (depending on your service provider, pre-defined menus may differ) or make a fake call (down); In Menu mode, scroll through menu options

▶ Make fake calls

Dial key Make or answer a call; In Idle mode, retrieve recently dialled, missed, or received numbers

0

Voice mail service key In Idle mode, access voice mails (press and hold)

Softkeys Perform actions indicated at the bottom of the display

Confirm key

In Idle mode, launch the web browser or access Menu mode; In Menu mode, select the highlighted menu option or confirm an input

Power/Menu exit key Turn the phone on and off (press and hold); End a call In Menu mode, cancel input and return to Idle mode

Alphanumeric kevs

0 Silent profile key In Idle mode, activate or deactivate the silent profile (press and hold)

Your phone displays the following status indicators on the top of the screen:

lcon	Description
Taul	Signal strength
C	Call in progress
¢	Call diverting activated
B	Roaming (outside of normal service area)
9	Alarm activated
E.	New text message (SMS)
	New voice mail message
4	Normal profile activated
剩	Silent profile activated
{	Battery power level

Install the SIM card and battery

1. Remove the battery cover and insert the SIM card.



2. Insert the battery and replace the battery cover.





Charge the battery

1. Plug the supplied travel adapter.

2. When charging is finished, unplug the travel adapter





Do not remove the battery from the phone before unplugging the travel adapter first. Otherwise, the phone may be damaged.

Turn your phone on or off

(represents the **OK** softkey)

To turn your phone on,

Instructional icons

message)

Note: notes, usage tips, or additional information

Followed by: the order of options or menus you must select to perform a step; for example: In Menu

mode, select Messages → Create new message

Square brackets: phone keys; for example: []

Angled brackets: softkeys that control different

functions at each screen; for example: <OK>

(represents Messages, followed by Create new

- 1. Press and hold [707]
- 2. Enter your PIN and press < **OK**> (if necessary).
- 3. Set the time and date and press <Save> (if

To turn your phone off, repeat step 1 above.



If you remove the battery, the time and date will be

Access menus

To access your phone's menus.

- 1. In Idle mode, press < Menu > to access Menu mode
- You may need to press the Confirm key to access Menu mode depending on your region or service provider
- 2. Use the Navigation key to scroll to a menu or option.
- 3. Press < Select>, < Save>, or the Confirm key to confirm the highlighted option.
- 4. Press <Back> to move up one level; Press [To] to



- When you access a menu requiring the PIN2, you must enter the PIN2 supplied with the SIM card. For details, contact your service provider
- Samsung is not responsible for any loss of passwords or private information or other damages caused by illegal software

Make a call

- 1. In Idle mode, enter an area code and a phone
- 2. Press [] to dial the number
- 3. To end the call, press [70]

Answer a call

- 1. When a call comes in, press [-].
- 2. To end the call, press [].

Adjust the volume

To adjust the volume of the ringtone

- 1. In Menu mode, select **Settings** \rightarrow **Profiles**.
- 2. Scroll to the phone profile you are using.



If you are using the silent or offline profile, you are not allowed to adjust the volume of the ringtone

- 3. Press <Options> → Edit → Volume
- 4. Scroll left or right to adjust the volume level.
- 5. Press <Save>

To adjust the volume of voice during a call


While a call is in progress, press the Navigation key up or down to adjust the volume.



In noisy environments, you may have difficulty hearing the calls while using the speakerphone feature. For better audio performance, use the normal phone mode.

Change your ringtone

- In Menu mode, select Settings → Profiles.
- 2. Scroll to the profile you are using.



- 3. Press <Options> → Edit → Call ringtone
- Select a ringtone category → a ringtone.
- To switch to another profile, select it from the list.

Call a recently dialled number

- 1. In Idle mode, press [-1]
- 2. Scroll left or right to a call type
- 3. Scroll up or down to a number or name.
- 4. Press the Confirm key to view details of the call or [] to dial the number

Enter text

To change the text input mode

- · Press and hold [#] to switch between T9 and ABC
- Press [#] to change case or switch to Number mode.
- Press [*] to switch to Symbol mode.
- Press and hold [*] to select an input mode or change the input language

T9 mode

- 1. Press appropriate alphanumeric keys to enter an entire word.
- 2. When the word displays correctly, press [0] to insert a space. If the correct word does not display, press the Navigation key up or down to select an alternate word.

ABC mode

Press an appropriate alphanumeric key until the character you want appears on the display.

Press an appropriate alphanumeric key to enter a number.

Symbol mode

Press an appropriate alphanumeric key to enter a



- To delete characters one by one, press <Clear>. To delete the characters on the left side of the cursor,
- press and hold <Clear>. To insert a space between characters, press [0].
- . To enter punctuation marks, press [1].



memory. To change the memory location, in Menu mode, select Phonebook → Management → Save new contact to → a memory location

- 2. Select Create contact.
- 3. Select a number type (if necessary).
- 4 Enter contact information
- 5. Press the Confirm key to add the contact to memory.

Send and view messages

To send a text message

- 1. In Menu mode, select Messages → Create new message
- 2. Enter a recipient number and scroll down.

4. Press the Confirm key to send the message

- 3. Enter your message text. ▶ Enter text
- To view text messages
- 1. In Menu mode, select Messages → Inbox.
- 2. Select a text message.

Make fake calls

To make a fake call

You can simulate an incoming call when you want to get out of meetings or unwanted conversations.

In Idle mode, press and hold the Navigation key down.

When someone inserts a new SIM card in your phone. the mobile tracker feature will automatically send the contact number to two recipients to help you locate and recover your phone. To activate the mobile tracker,

- 1. In Menu mode, select **Settings** → **Security** Mobile tracker.
- 2. Enter your password and press < OK >.

Activate the mobile tracker



The first time you access ${\bf Mobile\ tracker},$ you will be prompted to create and confirm a passwo

- 3. Scroll left or right to On.
- 4. Scroll down and press the Confirm key to open the
- 5. Press the Confirm key to open your contact list.
- 6. Select a contact.
- 7. Select a number (if necessary).
- 8. Press the Confirm key to save the recipients. 9. Scroll down and enter the sender's name.
- 10. Press the Confirm key → < Accept>.

Set and use alarms

To set a new alarm

- 1. In Menu mode, select Alarms

- 4. Press **Save**, or press **Options** \rightarrow **Save**.

To stop an alarm

When the alarm sounds.

- Press <OK> or the Confirm key to stop the alarm without snooze.
- · Press <OK> or the Confirm key to stop the alarm with snooze, or press < Snooze > to silence the alarm for

To deactivate an alarm

- 1. In Menu mode, select Alarms.
- 2. Select the alarm you want to deactivate
- 3. Scroll left or right to Off.

4. Press <Save>



- 2. Select an empty alarm location
- 3. Set alarm details
- the snooze period.

- - If the battery has been removed, the scheduled alarm



· To move the cursor, press the Navigation key.

- Add a new contact

Your phone is preset to save contacts to the phone

- 1. In Idle mode, enter a phone number and press

SAMSUNG ELECTRONICS



Declaration of Conformity (R&TTE) Samsung Electronics

GSM Mobile Phone: GT-E1150 to which this declaration relates, is in conformity with the following standards and/o

EN 60950-1 : 2006+A11:2009 EN 301 489-01 V1.8.1 (04-2008) EN 301 489-07 V1.3.1 (11-2005)

EN 301 511 V9 0 2 (03-2003) We hereby declare that [all essential radio test suites have been carried out and that] the above named product is in conformity to all the essential requirements o Directive 1999/5/EC.

Annex[IV] of Directive 1999/5/EC has been following Notified Body(ies):

BABT, Forsyth House Churchfield Road, Walton-on-Thames, Surrey, KT12 2TD, UK*

RADIO

The technical documentation kept at Samsung Electronics QA Lab

ich will be made available upon requepresentative in the EU) Samsung Electronics Euro QA Lab

Joong-Hoon Choi / Lab Manager * It is not the address of Samsung Service Centre. For the address or the phone

number of Samsung Service Centre, see the warranty card or contact the retaile where you purchased your product.