

PICCOLO ABS M 95 G



Sample photo

Order symbol: ABS M 95 G
Product nbr: 8784318
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002334
EI. number:
 Finland: 3423469
 Denmark: 8212002076
 Italy: 7211060
 Sweden: 2536729
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		230	140	95	Ingress Protection (EN 60529): IP 66/67
inch:		9.1	5.5	3.7	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		Flammability Rating (UL 746 C 5): UL 94 HB	
Cover colour:		RAL 7035		Glow Wire Test (IEC 695-2-1) °C: 650	
Cover screws material:		Polyamide		NEMA Class: NEMA 1, 4, 4X, 6, 6P, 12, 13	
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
M-MP		Mounting plate			
CHM-3		DIN-35 Mounting rail			
FM-3		DIN-35 Mounting rail			
FP 22046		Wall fastening lug (4 pcs)			

PICCOLO 230x140x95-125

