

# FM015

## TELCO Male Modular Connectors - RJ11 (6-Wire)

Status: Available

### FUNCTIONAL NOTES:

This TELCO Modular Connector is for use with Flat Satin Flat Oval cable or Solid conductor Round cable. According to the manufacturer of this connector it will accept a Flat Oval cable 0.090 inches high by 0.190 inches wide plus or minus 0.010 inches. It will also accept a Round cable with a Max 0.100 inch outside diameter. Wire gauges accepted are 24,26,or 28 AWG. Stranded can be 24 thru 28 AWG, Solid conductor cable can be 24 or 26 AWG.

### PRODUCT SPECIFICATIONS:

<b>Physical</b>	
<b>Weight</b>	
<b>Dimensions</b>	
<b>Connector Style</b>	RJ11
<b>Gender</b>	Male
<b>Termination Method</b>	Crimp Style
<b>Marketing</b>	
<b>Special Product Cross Reference</b>	EL06A (RJ11 Bulk Cable).
<b>Literature</b>	
<b>Manual Available?</b>	
<b>Manual Name</b>	
<b>Manual Date</b>	
<b>Schematic Vendor Name</b>	
<b>Schematic Available?</b>	
<b>Schematic Non-Disclosure Required?</b>	
<b>Schematic Date</b>	
<b>Additional Schematic Requirements</b>	
<b>Literature Comments</b>	
<b>Agency Compliance</b>	
<b>EIA/TIA</b>	