


SAMPLE PTSM 0,5/ 7-2,5-V-SMD

Order No.: 1701089

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1701089>

PCB terminal block, Nominal current: 6 A, Nom. voltage: 160 V,
Pitch: 2.5 mm, Number of positions: 7, Connection method: Spring-
cage conn., Mounting: SMD/THT/THR, Conductor/PCB connection
direction: 90 °

Commercial data

EAN	 4 046356 515092
Pack	5
Customs tariff	85369010
Gross weight in pieces	2.42 g
Country of Origin	DE

Product notes

WEEE/RoHS-compliant since:
08/06/2009



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions

Length	5 mm
Pitch	2.5 mm
Dimension a	15 mm
Pin spacing	2.5 mm

General

Range of articles	PTSM 0,5/..-V-SMD
Rated surge voltage (III/3)	2.5 kV

Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	32 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	6 A
Nominal cross section	0.5 mm ²
Solder pin surface	Sn
Stripping length	6 mm
Number of positions	7

Connection data

Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	20

Certificates

Certification

Certifications applied for:

Certification Ex:

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;