

**SOLID PC 2828 13 T**



Sample photo

**Order symbol:** PC 2828 13 T  
**Product nbr:** 5330062  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005519  
**EI. number:**  
 Finland: 3423813  
 Italy: 7402040  
 Sweden: 2539448  
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		278	278	130	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		10.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
<b>Material:</b>		Polycarbonate			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		Clear transparent			
<b>Cover screws material:</b>		Polyamide			
<b>Cover screws colour:</b>		Grey			
<b>Gasket material:</b>		Polyurethane			
Temperatures:					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
Accessories:					
EKOVT		Mounting plate			
EKOXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKOZR		Extension frame			
					<b>Certificates:</b>
					Underwriters Laboratories
					Fimko
					Europe EN 62208: 2003
					UL Canada
					Gost R

