

SOLID PC 5628 13 G-3FSH



Sample photo

Order symbol: PC 5628 13 G-3FSH
Product nbr: 2539525
Description: Enclosure, PC
Remarks: Grey hinged cover

EAN: 6418074052759
EI. number:
 Finland: 3435732
 Sweden: 2539525
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		558	278	130	Ingress Protection (EN 60529): IP 65
inch:		22.0	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKTVT		Mounting plate			
EKTXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKV 50		DIN-35 Mounting rail			
EKTZR		Extension frame			
					Certificates:
					Underwriters Laboratories
					Fimko
					Europe EN 62208: 2003
					UL Canada
					Gost R

