

SOLID PC 5638 18 T-3FSH



Sample photo

Order symbol: PC 5638 18 T-3FSH
Product nbr: 2539557
Description: Enclosure, PC
Remarks: Transparent hinged cover

EAN: 6418074052933
EI. number:
 Finland: 3435768
 Sweden: 2539557
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		558	378	180	Ingress Protection (EN 60529): IP 65
inch:		22.0	14.9	7.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		Clear transparent			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKUVT		Mounting plate			
EKUXT		Mounting plate Pertinax			
EKV 32		DIN-35 Mounting rail			
EKUZR		Extension frame			
					Certificates:
					Underwriters Laboratories
					Fimko
					Europe EN 62208: 2003
					UL Canada
					Gost R

SOLID 558x378x180

