

10 ft Black SuperSpeed USB 3.0 Cable A to B - M/M

StarTech ID: *USB3SAB10BK*



StarTech.com's 10ft Black SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 10ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 10ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electromagnetic interference and ensuring reliable data communication.

The 10ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Applications

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Molded connectors with strain relief

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Foil shielded twisted pair
Connector A	1 - USB 3.0 A (9 pin; SuperSpeed) Male
Connector B	1 - USB 3.0 B (9 pin; SuperSpeed) Male
Type and Rate	USB 3.0 - 5 Gbit/s
Color	Black
Wire Gauge	28 AWG
Cable Length	3 m [10 ft]
Operating Temperature	-10°C to 50°C (14°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Humidity	0~75% RH
Shipping (Package) Weight	130 g [4.6 oz]
Included in Package	1 - 10ft black USB 3.0 A to B cable

Certifications, Reports and Compatibility

