

## Black Box Products

---

Cables > Computer & Data Cables



### Extended-Distance Data Cable—Office Environment, PVC Jacket, 7 Conductors (3 1/2 Pairs), 500-ft. (152.4-m)



Send RS-232 data up to 500 feet in your office environment.

EDN07A-0500

---

Extended Double Diamond™ Warranty Available (Lifetime)

#### Product Highlights

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

## Details

### Description

Extended-Distance Data Cable—Office Environment, PVC Jacket, 7 Conductors (3 1/2 Pairs), 500-ft. (152.4-m)

### Quick Facts

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

## Tech Spec

Technical Specifications for Extended-Distance Data Cable—Office Environment, PVC Jacket, 7 Conductors (3 1/2 Pairs), 500-ft. (152.4-m):

<b>Cable Type</b>	— Twisted pair, PVC jacket
<b>Capacitance</b>	— 12 pF/ft. ± 2 pF/ft.
<b>Conductor Gauge</b>	— 24 AWG (7 x 32 AWG) stranded
<b>Resistance</b>	— 25 ohms/1000 ft.
<b>Shield</b>	— Foil wrap with drain wire