

Black Box Products

Cables > Computer & Data Cables

Extended-Distance Data Cable, Office Environment, PVC Jacket, 25 Conductors (12 1/2 Pairs), 500-ft. (152.4-m)



Send RS-232 data up to 500 feet in your office environment.

EDN25A-0500

Extended Double Diamond™ Warranty Available (Lifetime)

Product Highlights

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

Details

Description

Extended-Distance Data Cable, Office Environment, PVC Jacket, 25 Conductors (12 1/2 Pairs), 500-ft. (152.4-m)

Quick Facts

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

Tech Spec

Technical Specifications for Extended-Distance Data Cable, Office Environment, PVC Jacket, 25 Conductors (12 1/2 Pairs), 500-ft. (152.4-m):

Cable Type	— Twisted pair, PVC jacket
Capacitance	— 12 pF/ft. ± 2 pF/ft.
Conductor Gauge	— 24 AWG (7 x 32 AWG) stranded
Resistance	— 25 ohms/1000 ft.
Shield	— Foil wrap with drain wire