

RT4MPR

4 pole TINY xlr male chassis connector, rearmountable, nickel housing, gold plated contacts, max. panel thickness: 3 mm



Technical Information

Product

Title RT4MPR

Electrical

Contact resistance < 5 m Ω (inner)
Dielectric strength > 0.5 kVdc
Insulation resistance > 1 G Ω
Rated current per contact < 5 A

Mechanical

Lifetime > 1000 mating cycles
Panel thickness max. 3 mm
Wiresize 0.22 mm²
Wiresize 24 AWG

Environmental

Temperature range -30 °C to +85 °C