

RT5MC-B

5 pole TINY xlr male cable connector, black metal shell, gold plated contacts, bulk packaging available (*-D)



Technical Information

Product

Title RT5MC-B

Electrical

Contact resistance < 5 m Ω (inner)
Dielectric strength > 0.5 kVdc
Insulation resistance > 1 G Ω
Rated current per contact < 5 A

Mechanical

Cabel O.D. 2.0 - 4.5 mm
Lifetime > 1000 mating cycles
Wiresize 0.22 mm²
Wiresize 24 AWG

Material

Strain relief PVC

Environmental

Temperature range -30 °C to +85 °C