

RBK SWO 8" ADJUSTABLE



Features and Benefits

With 50% less weight and extra wide opening jaws these adjustable wrenches are ideal for Plumbing, heating, ventilation, air conditioning and most MRO engineering applications

The extra long and slimmer jaws provide greater accessibility in tight confined spaces

Manufactured from chrome vanadium steel, with a phosphated finish

The Ergotop grip provides extra comfort and helps reduce hand fatigue

These wrenches exceed the requirements of DIN3117,ISO6787-2001 (180Nm torque) and ASME B107.8-2003 (305Nm torque)

Facts The 6" is 78% wider than a standard 6" adjustable and 68% lighter than a standard 12" with a similar opening

The 8" is 62% wider than a standard 8" adjustable and 50% lighter than a standard 12" with a similar opening

Product Attributes

Capacity, jaw Imperial	1-1/2
Capacity, jaw max	39 mm
Description, Product	216
Diameter, bore nom	8
Diameter, outside	39
Jaw opening	1-1/2
Length	216
Length	200 mm
Length, Inches	8 "
Material	Chrome vanadium steel
RoHS Compliant	NA
Weight	305 kg