

MINIATURE LAMP (356) Details



Part #	356				
Description	G3 1/2 M BAY 28V .17A 3.5CP				
Bulb Shape	G-3 1/2	Filament	C-2F	Base Style	Miniature Bayonet (BA9s)
Glass Diameter (in)	0.46	MOL[†] (in)	0.94	LCL^{††} (in)	0.50
Glass Diameter (mm)	11.7	MOL (mm)	23.88	LCL (mm)	12.70
Volts	28	MSCP[‡]	3.5	Avg Life Hrs	500
Watts	4.76	Amps	0.17	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source