

## MINIATURE LAMP (656) Details



<b>Part #</b>	656				
<b>Description</b>	T3 1/4 WEDGE 28V .06A .62CP				
<b>Bulb Shape</b>	T-3 1/4	<b>Filament</b>	C-2F	<b>Base Style</b>	Wedge (T-3 1/4)
<b>Glass Diameter (in)</b>	0.39	<b>MOL<sup>†</sup> (in)</b>	1.06	<b>LCL<sup>††</sup> (in)</b>	0.56
<b>Glass Diameter (mm)</b>	10	<b>MOL (mm)</b>	26.80	<b>LCL (mm)</b>	14.20
<b>Volts</b>	28	<b>MSCP<sup>‡</sup></b>	0.62	<b>Avg Life Hrs</b>	2500
<b>Watts</b>	1.68	<b>Amps</b>	0.06	<b>RoHS Compliant</b>	Yes

**† MOL (Maximum Overall Length):**

The overall length of a lamp, from the top of the shell to the bottom of the base.

**‡ MSCP (Mean Spherical Candlepower):**

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

**†† LCL (Light Center Length):**

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.