

MINIATURE LAMP (90MB) Details



Part #	90MB				
Description	T2 1/2 90V .03A BA9S				
Bulb Shape	T-2 1/2	Filament	CC-7A	Base Style	Miniature Bayonet (BA9s)
Glass Diameter (in)	0.31	MOL[†] (in)	1.19	LCL^{††} (in)	0.63
Glass Diameter (mm)	7.9	MOL (mm)	30.20	LCL (mm)	16.00
Volts	90	MSCP[‡]	4.65	Avg Life Hrs	5000
Watts	2.7	Amps	0.03	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.