

MINIATURE LAMP (912) Details



| Part # | 912 | | | | |
|---------------------|------------------------|-----------------------|-------|------------------------|-------------|
| Description | T5 WEDGE 12.8V 1A 12CP | | | | |
| Bulb Shape | T-5 | Filament | C-2R | Base Style | Wedge (T-5) |
| Glass Diameter (in) | 0.63 | MOL [†] (in) | 1.49 | LCL ^{††} (in) | 0.81 |
| Glass Diameter (mm) | 16 | MOL (mm) | 37.80 | LCL (mm) | 20.60 |
| Volts | 12.8 | MSCP [‡] | 12 | Avg Life Hrs | 1000 |
| Watts | 12.8 | Amps | 1.00 | RoHS Compliant | Yes |

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.