



Tenma 72-10390

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	200mV/2000mV/20V/200V/250V	±(0.5%+2)
AC Voltage	200V/250V	±(1.2%+3)
DC Current	2000μA/20mA/200mA/10A	±(1%+2)
Resistance	200 Ω /2kΩ/20kΩ/200kΩ/2000kΩ/20MΩ	±(1.2%+3)
Temperature(°C)	-40°C~1000°C	±(1.0%+3)
Special Functions		
Display Count		1999
Manual Range		√
Diode		√
Transistor		√
Continuity Buzzer		√
Low Battery Indication		√
Data Hold		√
Input Impedance for DCV	Around :10MΩ	√

GENERAL CHARACTERISTICS

Power	9V Battery (6F22)	
LCD Size	49 x 18mm	
Product Colour	Orange and Grey	
Product Net Weight	200g	
Product Size	72 x 137 x 35mm	
Standard Accessories	Battery, Test Lead, Multi-Purpose Socket, Point Contact Temperature Probe	
Standard Individual Packing	Gift Box , English Manual	
Standard Quantity Per Carton	40pcs	
Standard Carton Measurement	540 x 365 x 290mm(0.057 CBM Per Standard Carton)	
Standard Carton Gross Weight	13.8kg	