



Drawings not to scale  
All dimensions in mm (inches) nominal

## SPECIFICATION

CONTACT FORM/STYLE		Closed
SWITCHING VOLTAGE	Max. Vac	130
SWITCHING CURRENT	Max. A	0.25
SWITCHING CAPACITY	Max. VA	3
CONTACT RESISTANCE	Max. mΩ	100
SWITCHING DISTANCE	Min. mm	Dependant on magnet
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-25° +70°
CASE MATERIAL		Polypropylene

## PROXIMITY SENSORS

PART NUMBER  
**PPS 130B**

Rev. No.	Revision Note	Date	Signature
A	Web Site 2000	1-6-00	RG

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.

The Comus Group of Companies consist of:  
Assemtch Europe Limited  
E. Bachem GmbH  
Comus International  
W. Gunther GmbH  
Gunther Belgium  
Gunther France  
S.T.G.