

ARCA 405021



Sample photo

Order symbol: ARCA 405021
Product nbr: 8120025
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the short side

EAN: 6418074079367
EI. number:
 Finland: 3423123
 Denmark: 8212091236
 Sweden: 2500115
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		400	500	210	Ingress Protection (EN 60529): IP 66
inch:		15.7	19.7	8.3	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		PUR			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 5040		Mounting plate			
MPP ARCA 5040		Mounting plate perforated			
MPX ARCA 5040		Mounting plate			
DRS ARCA 405021		DIN rail frame set			
PMK ARCA 50		Pole mounting kit			
Certificates:		Fimko			

ARCA 500x400x210

ARCA 400x500x210

