



Part Number : **L08-01AAS-MR7001**
Pin :
Connector Body : Copper Alloy, Nickel Plated
Temperature Range : -20°C~105°C

Description	Details
Connector	LED(M8)
Number of Contacts	1 pins
Assy Style	Solder
Connector body type	Rear Fastened (See more details)
Back shell	Circular
Waterproof Rating	IP67, Unmated
Size	M8
No. of LED	1
Color of LED	Red / Green
LED Dim	φ3.0mm
Electrical Material	DC 4V
LED Housing Material	Metal
流水號	001
Panel Cut φ	φ8.1~7.1
Panel Thickness	6.5

Mating Parts

Receptacle
 Overmolded with cable
 Field installable

Accessories