

Cover for Holder OG (Clip) 5x20, OG (Halter) 5x20, UH, UHB



References

Mating cover to OG (Clip) 5x20; OG (Holder) 5x20; UH; UHB



Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Fuse-Link	5 x 20 mm
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cover	Thermoplastic Transparent UL 94V-0
Storage Conditions	0 °C to 60 °C, max. 70% r.h.

Dimension



Variants

Description	Order Number
Transparent Cover 1.6 W	0853.9561
Transparent Cover 2.5 W	0853.9562

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging Unit

Plastic Bag (100 pcs.)