

Canon PIXMA MX475

Home office All-In-One with wireless connectivity and Auto Document Feeder

Print, copy, scan and fax with ease using this affordable Wi-Fi All-In-One. Share functions between multiple PCs as well as mobile devices and enjoy the optional cost effective XL ink cartridges.

- Affordable All-In-One printer with print, copy, scan and fax functions
- Wireless connectivity for easy sharing around the home or office
- Quick processing of multipage documents with 30 sheet Auto Document Feeder
- PIXMA Printing Solutions app, Google Cloud Print and Apple AirPrint support
- Enjoy A4 document print speed of 9.7 ipm mono/5.5 ipm colour

• **PRINTER SPECIFICATIONS**

Print Resolution	Up to 4800 ¹ x 1200 dpi
Print Technology	2 FINE Cartridges (BK, CL) Inkjet system with 2pl (min.) ink droplet size ChromaLife100 inks
Mono Document Print Speed	Approx. 9.7 ipm ¹
Colour Document Print Speed	Approx. 5.5 ipm ¹
Photo Print Speed	Borderless 10x15cm: Approx. 46 seconds ¹
Borderless Printing	Yes (A4, LTR, 20x25cm, 13x18cm, 10x15cm)
Two Sided Printing	Manual

• **SCANNER SPECIFICATIONS**

- [Back to Top](#)

Scanner Type	Flatbed, ADF and CIS colour scanner
Scanner Resolution (Optical)	Up to 1200 x 2400 dpi ¹
A4 Scan Speed	Approx. 15 seconds ¹
Maximum Document Size	Flatbed: A4, LTR (216x297mm) ADF: A4, LTR, LGL
OCR	Yes
Scanning Depth (Input / Output)	Colour: 48 bit / 24 bit Greyscale: 16 bit / 8 bit

• **COPIER SPECIFICATIONS**

- [Back to Top](#)

Copy Speed Colour Document	sFCOT: Approx. 24 seconds ¹ sESAT: Approx. 4.7 ipm ¹ sESAT ADF: Approx. 4.3 ipm ¹
Multiple Copy	1 to 99 pages
Copy zoom	25-400%
Copy functions	Document Copying, Photo Copying, Fit-to-Page Copying, Borderless Copying
Copy quality settings	Fast, Standard, High

- **FAX SPECIFICATIONS**

- [Back to Top](#)

Fax Type	Super G3 / Colour
Fax Resolution	Mono: up to 300 x 300dpi Colour: 200 x 200 dpi
Fax Speed	Mono: approx. 3 sec. (33.6kbps) ¹ Colour: approx. 1 min. (33.6kbps) ¹
Fax Memory	Up to 50 pages

- **COMPATIBLE INKS**

- [Back to Top](#)

Standard Ink Cartridges	PG-540 (Black) CL-541 (Colour)
Optional XL Ink Cartridges	PG-540XL (Black XL) CL-541XL (Colour XL)

- **INK YIELDS**

- [Back to Top](#)

BK (Pigment Black)	Standard: 180 document pages or 2,465 photos* Optional XL: 600 document pages or 7,560 photos*
CL (Colour - CMY)	Standard: 180 document pages or 69 photos Optional XL: 400 document pages or 150 photos
Testing standards	ISO/IEC 24711 for A4 colour document pages ISO/IEC 29102 for 10x15cm colour borderless photos Values obtained by continuous printing * Estimated supplemental yield

- **PAPER SUPPORT**

- [Back to Top](#)

Paper Types	Plain Paper Envelopes (DL, COM10) Canon Pro Platinum (PT-101) Canon Pro Luster (LU-101) Canon Plus Glossy II (PP-201) Canon Plus Semi-gloss (SG-201) Canon Glossy Everyday Use (GP-501) Canon Matte (MP-101) Canon High Resolution Paper (HR-101N) Canon Photo Stickers (PS-101) Canon T-Shirt Transfer (TR-301)
Maximum Paper Input	Max. 100 sheets of plain paper Max. 20 sheets of photo paper
Paper Sizes	A4, A5, B5, LTR, LGL, 20x25cm, 13x18cm, 10x15cm
Paper Weight	Plain paper: 64 - 105 g/m ² Canon photo paper up to 300 g/m ² (PT-101)

- **CONNECTIVITY**

- [Back to Top](#)

Wired Connections	Hi-Speed USB
Wireless Connections	Wi-Fi IEEE802.11 b/g/n ¹ Access Point Mode
Applications Support	PIXMA Printing Solutions app ¹ Apple AirPrint Google Cloud Print

- **SOFTWARE**

- [Back to Top](#)

Supported Operating	Windows 8.1 / 8 / 7 / Vista SP1 & SP2 / XP SP3 32-bit
---------------------	---

Systems	Mac OS X v10.6.8 or later
Supported Mobile Systems	iOS (PIXMA Printing Solutions app, AirPrint) Android (PIXMA Printing Solutions app) Windows RT
Minimum System Requirements	Windows: Internet Explorer 8, internet connection or CD-ROM Mac: Safari 5 and internet connection Display: 1024 x 768 XGA
Software Included	MP Driver with Scanning Utility Quick Menu My Image Garden Easy-WebPrint EX (plug-in for IE8 or higher)

- **PHYSICAL FEATURES**

- [Back to Top](#)

Display Type & Size	Full dot LCD display
Display languages	English, German, French, Italian, Spanish, Dutch, Portuguese, Norwegian, Swedish, Danish, Finnish, Russian, Czech, Hungarian, Polish, Slovene, Turkish, Greek, Slovakian, Estonian, Latvian, Lithuanian, Ukrainian, Romanian, Bulgarian, Croatian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Indonesian
Automatic Document Feeder	Up to 30-sheets
Dimensions (W x D x H)	458 x 385 x 200 mm
Weight	8.4kg
Power Source	AC 100-240V, 50/60Hz
Power Consumption	Standby: Approx. 1.0 W (Wi-Fi connection to PC) Off: Approx. 0.3 W Copying: Approx. 18 W ¹
Acoustic Noise Levels	Approx. 43.0 dB(A) ¹
Recommended Operating Environment	Temperature: 15-30°C Humidity: 10-80%RH (no dew condensation)
Duty Cycle	up to 3,000 pages / month