

Black Box Products

Industrial > Cabling & Infrastructure

Bulk Extended-Distance/Quiet Cable— Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 1000-ft. (304.8-m)



Send RS-232 data up to 500 feet in noisy environments

EMN04A-1000

Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!

Details

Description

Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 1000-ft. (304.8-m)

Quick Facts

- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!

Further Details

Ideal for noisy environments where cable runs are next to power lines and other cabling systems that cause interference.

Tech Spec

Technical Specifications for Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 1000-ft. (304.8-m):

Cable Type	Twisted pair, PVC jacket
Capacitance	12 pF/ft. ± 2 pF/ft.
Conductor Gauge	24 AWG (7 x 32 AWG) stranded
Resistance	25 ohms/1000 ft.
Shield	One foil and one copper braid

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight.