

Digital laser measure

PLR 15

Switch on, measure, done!

[Go to product](#)



Key product features

- Precise measurement of lengths and distances with laser technology
- Intuitive handling thanks to easy one-button operation
- Small, compact and handy for any trouser pocket

Other product advantages

- Easy-to-read display with backlighting
- Measuring up to 15 m
- Hold function to save the last measured value
- Softgrip for comfortable handling

Comes complete with

- 2 x 1.5 V LR03 (AAA) batteries

Part number: 0603672000

EAN code: 3165140727754

Digital laser measure

PLR 15

Technical data

Laser diode: 635 nm

Laser class: 2

Measurement range: 0,15 – 15,00 m

Measurement accuracy, typical: $\pm 3,0$ mm

Measurement time, typical: 0,5 s

Measurement time, max.: 4 s

Battery: 2 x 1.5 V LR03 (AAA)

Automatic deactivation: 5 min

Weight: 0,08 kg

Functions



Laser technology

Maximum precision when working

Functions

Distance measurement