



NOTE: End Cap to be impression stamped with "JKL and applicable PART NUMBER."

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
GF540	6.0	.100	.10	1.26	10,000	C-8
GF550	6.0	.200	.40	5.03	5,000	C-8
GF570	6.3	.250	.64	8.04	10,000	C-8
GF560	6.3	.300	.64	8.04	10,000	C-8
GF660	8.0	.150	.40	5.03	10,000	C-8
GF665	8.0	.200	.25	3.14	10,000	C-8
GF670	8.0	.250	.64	8.04	10,000	C-8
GF680	8.0	.300	.90	11.31	10,000	C-8
GF710	12.0	.100	.23	2.89	10,000	C-8
GF780	12.0	.150	.70	9.00	5,000	C-8
GF740	12.6	.300	.64	8.04	5,000	C-8

METRIC

DIMENSIONS ARE IN MILLIMETERS

TOLERANCE UNLESS OTHERWISE SPECIFIED

1 PL +/- 0.2

2 PL +/- 0.20

ANGLE +/-

THIRD ANGLE PROJECTION

DRAWN BY L. WENGSTROM

APPVD BY ED

DATE 3/1/01

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

JKL COMPONENTS CORPORATION

TITLE: T-2 FUSE STYLE (3AG) LAMPS

SIZE: A

FORM NO.: 55335

DRAWING NO.: FUSE GF SERIES T-2

SCALE: NONE

RELEASED DATE: 3/1/01

REVISION DATE:

REV. NO.:

SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
RELEASED		3/1/01