

Melf Chip Resistors

SBR-101

(4 Flap FL24/10) 93 Values / 4.185 Pieces

Type/Fab: ZC0207 / Vitrohm

Watt: 1W

Tolerance: ±1/2%

TK: 50ppm/°C

Size: 0207

Quantity: 45 Pieces / Value

Range: 0,22 Ohm -10M Ohm (E-12 Serie)

Binder: 1 x CCO-50 (Dimension: 318x260x50)

Values:

0R22	0R27	0R33	0R39	0R47	0R56
0R68	0R82	1,0 R	1,2R	1,5 R	1,8R
2,2 R	2,7R	3,3 R	3,9R	4,7 R	5,6R
6,8 R	8,2R	10 R	12 R	15 R	18 R
22 R	27 R	33 R	39 R	47 R	56 R
68 R	82 R	100 R	120 R	150 R	180 R
220 R	270 R	330 R	390 R	470 R	560 R
680 R	820 R	1,0 K	1,2 K	1,5 K	1,8 K
2,2 K	2,7 K	3,3 K	3,9 K	4,7 K	5,6 K
6,8 K	8,2 K	10 K	12 K	15 K	18 K
22 K	27 K	33 K	39 K	47 K	56 K
68 K	82 K	100 K	120 K	150 K	180 K
220 K	270 K	330 K	390 K	470 K	560 K
680 K	820 K	1,0 M	1,2M	1,5 M	1,8M
2,2 M	2,7 M	3,3 M	3,9M	4,7 M	5,6 M
6,8 M	8,2M	10M			

REV: 12.06.2014