



Sample photo

**Order symbol:** ALN 162609  
**Product nbr:** 7811290  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074016133  
**EI. number:**  
Finland: 3420052  
Denmark: 8212045729  
Sweden: 2536327  
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		263	162	91	Ingress Protection (EN 60529): IP 66/67/68
<b>inch:</b>		10.4	6.4	3.6	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Material:</b>	Aluminium				<b>Certificates:</b> Fimko Gost R
<b>Base colour:</b>	RAL 7001				
<b>Cover colour:</b>	RAL 7001				
<b>Cover screws material:</b>	Stainless steel				
<b>Gasket material:</b>	Polyurethane				
<b>Temperatures:</b>					
<b>Short term:</b>	-50 ... 140 °C				
<b>Continuous:</b>	-50 ... 80 °C				
<b>Short term:</b>	-60 ... 285 °F				
<b>Continuous:</b>	-60 ... 175 °F				
<b>Accessories:</b>					
AM 1626	Mounting plate				
ARM 0825	DIN-15 Mounting rail				
ARH 26	DIN-35 Mounting rail				
MR 75005	Selftapping taptite screw M5				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

