



Black Box Products

Cables > Computer & Data Cables

Extended-Distance Data Cable, Office Environment, PVC Jacket, 16 Conductors (8 Pairs), Custom Lengths



Send RS-232 data up to 500 feet in your office environment.
EDN16A
Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!



Description

Extended-Distance Data Cable, Office Environment, PVC Jacket, 16 Conductors (8 Pairs), Custom Lengths

Quick Facts

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

Technical Specifications for Extended-Distance Data Cable, Office Environment, PVC Jacket, 16 Conductors (8 Pairs), Custom Lengths:

"

Cable Type	Twisted pair, PVC jacket
Capacitance	12 pF/ft. ± 2 pF/ft.
Conductor Gauge	24 AWG (7 x 32 AWG) stranded
Resistance	25 ohms/1000 ft.
Shield	Foil wrap with drain wire

Cross Reference

EDN16A-0500 – 50ft
EDN16A-2000 – 2000ft

