

Surface Mount Fuse with Holder, 12 x 5.2 mm, Quick-Acting F, 63 VAC, 63 VDC



UL 248-14 · 63 VAC · 63 VDC · Quick-Acting F



### Description

- Directly solderable on printed circuit boards
- OMK 63 = OMF 63 + OMH 125

### Standards

- UL 248-14
- CSA C22.2 no. 248.14


### References

[Packaging Details](#)

### Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)



### Technical Data

Rated Voltage	63 VAC, 63 VDC
Rated current	0.063 - 5 A
Breaking Capacity	50 A
Characteristic	Quick-Acting F
Mounting	PCB,SMT
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Housing	Thermoplastic, UL 94V-0
Material: Terminals	Tin-Plated Copper
Unit Weight	0.48 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 Type, Current, Approvals

Soldering Methods	Reflow
Solderability	245 °C / 3 sec acc. to IEC 60068-2-58, Test Td
Resistance to Soldering Heat	260 °C / 10 sec acc. to IEC 60068-2-58, Test Td

### Dimension

 12 mm




Soldering pads

### Pre-Arcing Time

Rated Current  $I_n$     1.0 x  $I_n$  min.    2.0 x  $I_n$  max.    4.0 x  $I_n$  max.

0.063 A - 5 A	4 h	1 s	10 ms
---------------	-----	-----	-------

Time-Current-Curves



All Variants

Fuse	Holder	Rated Current [A]	Rated Voltage [VAC]	Rated Voltage [VDC]	Breaking Capacity	Voltage Drop 1.0 I <sub>n</sub> typ. [mV]	Power Dissipation 1.0 I <sub>n</sub> typ. [mW]	Melting I <sup>2</sup> t 4.0 I <sub>n</sub> typ. [A <sup>2</sup> s]	Order Number
●	●	0.063	63	63	1)	2550	160	0.00011	3422.0003.xx
●	●	0.1	63	63	1)	1770	180	0.00067	3422.0004.xx
●	●	0.125	63	63	1)	1770	220	0.0011	3422.0049.xx
●	●	0.16	63	63	1)	1700	270	0.0018	3422.0005.xx
●	●	0.25	63	63	1)	990	250	0.0058	3422.0006.xx
●	●	0.35	63	63	1)	990	350	0.0076	3422.0043.xx
●	●	0.375	63	63	1)	990	370	0.013	3422.0044.xx
●	●	0.4	63	63	1)	960	380	0.016	3422.0007.xx
●	●	0.63	63	63	1)	290	180	0.02	3422.0008.xx
●	●	0.75	63	63	1)	260	200	0.031	3422.0046.xx
●	●	1	63	63	1)	220	220	0.078	3422.0009.xx
●	●	1.25	63	63	1)	220	280	0.14	3422.0010.xx
●	●	1.5	63	63	1)	200	300	0.24	3422.0047.xx
●	●	2	63	63	1)	200	400	0.44	3422.0012.xx
●	●	2.5	63	63	1)	190	480	0.97	3422.0013.xx
●	●	3	63	63	1)	190	570	1.3	3422.0014.xx
●	●	3.15	63	63	1)	190	600	1.2	3422.0048.xx
●	●	3.5	63	63	1)	140	490	1.6	3422.0015.xx
●	●	4	63	63	1)	140	560	2.1	3422.0016.xx
●	●	5	63	63	1)	140	700	2.9	3422.0017.xx

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 50 A @ 63 VAC/DC

Packaging Unit

.xx = .11 Plastic Bag (100 pcs.)  
.xx = .23 Blister Tape 33 cm Reel (1500 pcs.)