

Miniature Fuse, 4.7 x 16 mm, 125 VAC



125 VAC · Quick-Acting F



GAM  
T1 NNO

### Description

- Low Breaking Capacity


### References

Corresponding Fuseholder 231600P

### Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Technical Data

Rated Voltage	125 VAC
Rated current	0.063 - 10 A
Breaking Capacity	35 A
Characteristic	Quick-Acting F
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 70 °C
Climatic Category	40/070/56 acc. to IEC 60068-1
Material: Tube	Glass
Unit Weight	1.1 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 , Current

Resistance to Vibration	acc. to NF C 20-706 / IEC 60068-2-6, test Fc
-------------------------	--


### Dimension



### Pre-Arcing Time

Rated Current In	1.1 x In min.	1.7 x In max.	3.0 x In max.
0.063 A - 10 A	60 min	60 min	200 ms

**Time-Current-Curves**



**All Variants**

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 I <sub>n</sub> typ. [mV]	Power Dissipation 1.1 I <sub>n</sub> typ. [mW]	Melting I <sup>2</sup> t 10.0 I <sub>n</sub> typ. [A <sup>2</sup> s]	GAM T1 NNO	Order Number
0.063	125	1)	1900	140	0.00044		7010.2110
0.08	125	1)	1400	150	0.001		7010.2120
0.1	125	1)	1200	155	0.0015	● ●	7010.2130
0.15	125	1)	960	190	0.0067	● ●	7010.2150
0.2	125	1)	870	240	0.012	● ●	7010.2170
0.25	125	1)	795	270	0.025	● ●	7010.2180
0.31	125	1)	825	360	0.036	● ●	7010.2190
0.4	125	1)	1950	955	0.03	●	7010.2210
0.5	125	1)	1500	905	0.079	● ●	7010.2220
0.63	125	1)	2200	1650	0.092	● ●	7010.2230
0.75	125	1)	1700	1550	0.13	● ●	7010.2240
1	125	1)	275	385	0.2	● ●	7010.2260
1.5	125	1)	270	560	0.63	● ●	7010.2410
2	125	1)	175	470	1.2	● ●	7010.2430
2.5	125	1)	155	515	3.4	● ●	7010.2440
4	125	1)	210	1160	7.8	● ●	7010.2470
5	125	1)	145	935	14	● ●	7010.2480
6.3	125	1)	130	1040	31	●	7010.2610
8	125	1)	100	1060	68		7010.2620

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 35 A @ 125 VAC , p.f. ≥ 0.9

**Packaging Unit**    Small Box Pack (10 pcs.)