

Canon PIXMA MX725

Premium, high productivity 5-ink, All-In-One with Ethernet and Wi-Fi

A premium 5-ink wireless All-In-One featuring Ethernet, mobile and cloud connectivity plus a 35 sheet 2-sided ADF for highly productive printing, scanning, copying and faxing at home or in the office.

- Premium 5-ink All-In-One: print, copy, scan and fax
- Productive 250-sheet paper cassette and 2-sided 35 sheet ADF
- Easily share around the office with Wi-Fi and Ethernet connectivity
- Print from, and scan to mobile devices with PIXMA Printing Solutions app
- PIXMA Cloud Link, Google Cloud Print and Apple AirPrint support

Wireless printing

With Wi-Fi and AirPrint support you can print from smartphones, tablets and Apple devices.

- [Learn More](#)

Premium Quality Printers

Unique printing and ink technologies in PIXMA printers give outstanding, high quality prints.

- [Learn More](#)

Sign up to the FREE Canon Newsletter

Get free monthly news about products and software

[Sign up now](#)

Premium All-In-One

Stylish and productive this premium office All-In-One offers exceptional quality print, copy, scan and fax functions and is ideal for sharing between multiple PCs using either a wireless or Ethernet connection.

Double front cassettes with 250-sheet capacity plus a fully-integrated 35-sheet 2-sided Automatic

Document Feeder ensure maximum productivity.

Smart device and cloud printing

Download PIXMA Printing Solutions app and enjoy printing from, and scanning to, your smart devices over the Wi-Fi network. Directly from the printer screen you can browse and print photos from your Picasa online album, as well as calendars, stationery and other templates from the PIXMA Cloud. Google Cloud Print and Apple AirPrint are also supported.

Superior quality fast printing

With the 5 single ink system you only need to change the colour that runs out - making printing more efficient. Canon's FINE technology with up to 9600dpi print resolution delivers ultra-sharp text and images with great levels of detail. Enjoy A4 document print speeds of 15 ipm mono or 10 ipm colour and a 10x15cm borderless photo in approx. 21 seconds.

Save money on ink and paper

Print more for less. Optional XL and XXL inks deliver significantly more pages (up to 1000 with the XXL black ink) and last longer between ink replacements – ideal if you print frequently - offering up to 30%

savings per page compared to their standard equivalents. Auto 2-sided printing reduces paper usage and creates professional double-sided documents.

User-friendly operation

A 6.2cm colour display makes it easy to view selected functions and preview scanned documents and images. The Dual Function Panel features LED-lit, dual-purpose keys, which change appearance with selected mode, reducing the number of physical keys required.

PRINTER SPECIFICATIONS

Print Resolution	Up to 9600 ¹ x 2400 dpi
Print Technology	5 Individual Inks (PGBK, BK, C, M, Y) Inkjet FINE print head with 1pl (min.) ink droplet size ChromaLife100+ inks
Mono Document Print Speed	Approx. 15.0 ipm ¹
Colour Document Print Speed	Approx. 10.0 ipm ¹
Photo Print Speed	Borderless 10x15cm: Approx. 21 seconds ¹
Borderless Printing	Yes (A4, LTR, 20x25cm, 13x18cm, 10x15cm)
Two Sided Printing	Automatic

SCANNER SPECIFICATIONS

[Back to Top](#)

Scanner Type	Flatbed, ADF and CIS colour scanner
Scanner Resolution (Optical)	Up to 2400 x 4800 dpi ¹
A4 Scan Speed	Approx. 14 seconds ¹
Maximum Document Size	Flatbed: A4, LTR (216x297mm) ADF: A4, LTR, LGL
OCR	Yes
Scanning Depth (Input / Output)	Colour: 48 bit / 24 bit Greyscale: 16 bit / 8 bit

COPIER SPECIFICATIONS

[Back to Top](#)

Copy Speed Colour Document	sFCOT: Approx. 12 seconds ¹ sESAT: Approx. 8.4 ipm ¹
----------------------------	---

	sESAT ADF: Approx. 8.0 ipm ¹
Multiple Copy	1 to 99 pages
Copy zoom	25-400%
Copy functions	Document Copying, Photo Copying, Fit-to-Page Copying, Borderless Copying
Copy quality settings	Fast, Standard, High

FAX SPECIFICATIONS

[Back to Top](#)

Fax Type	Super G3 / Colour
Fax Resolution	Mono: up to 300 x 300dpi Colour: 200 x 200 dpi
Fax Speed	Mono: approx. 3 sec. (33.6kbps) ¹ Colour: approx. 1 min. (33.6kbps) ¹
Fax Memory	Up to 250 pages
Coded Speed Dialling	Max. 100 locations
Group Dial	Max. 99 locations

COMPATIBLE INKS

[Back to Top](#)

Standard Ink Cartridges	PGI-550PGBK (Pigment Black) CLI-551BK (Black) CLI-551C (Cyan) CLI-551M (Magenta) CLI-551Y (Yellow)
Optional XL Ink Cartridges	PGI-555PGBK XXL (Pigment Black) PGI-550PGBK XL (Pigment Black) CLI-551BK XL (Black) CLI-551C XL (Cyan) CLI-551M XL (Magenta) CLI-551Y XL (Yellow)

INK YIELDS

[Back to Top](#)

PBK (Pigment Black)	Standard: 375 document pages or 2,300* photos Optional XL: 620 document pages or 4,600* photos Optional XXL: 1,000 document pages or 7,500* photos
BK (Black)	Standard: 1,645* document pages or 421* photos Optional XL: 5,000* document pages or 1,130 photos
C (Cyan)	Standard: 332 document pages or 121 photos Optional XL: 700 document pages or 270 photos
M (Magenta)	Standard: 333 document pages or 140 photos

	Optional XL: 670 document pages or 313 photos
Y (Yellow)	Standard: 329 document pages or 120 photos Optional XL: 700 document pages or 271 photos
Composite (CMY average)	Standard CMY: 331 document pages or 126 photos Optional XL CMY: 690 document pages or 283 photos
Testing standards	ISO/IEC 24711 for A4 colour document pages ISO/IEC 29102 for 10x15cm colour borderless photos Values obtained by continuous printing * Estimated supplemental yield

PAPER SUPPORT

[Back to Top](#)

Paper Types	Plain Paper Envelopes (DL, COM10) Canon Pro Platinum (PT-101) Canon Pro Luster (LU-101) Canon Plus Glossy II (PP-201) Canon Plus Semi-gloss (SG-201) Canon Glossy Everyday Use (GP-501) Canon Matte (MP-101) Canon High Resolution Paper (HR-101N) Canon Photo Stickers (PS-101) Canon T-Shirt Transfer (TR-301)
Maximum Paper Input	Lower cassette: Max. 250 sheets of plain paper Upper cassette: Max. 20 sheets of photo paper
Paper Sizes	Lower cassette: A4, A5, B5, LTR, LGL, 20x25cm Upper cassette: 10x15cm, 13x18cm
Paper Weight	Plain paper: 64 - 105 g/m ² Canon photo paper up to 300 g/m ² (PT-101)

CONNECTIVITY

[Back to Top](#)

Wired Connections	Hi-Speed USB Ethernet 10/100Mbps (auto switchable) USB flash memory port
Wireless Connections	Wi-Fi IEEE802.11 b/g/n ¹ Bluetooth v 2.0 (optional USB adapter)
Applications Support	PIXMA Printing Solutions app ¹ Apple AirPrint Google Cloud Print Wireless PictBridge Print from Email

SOFTWARE

[Back to Top](#)

Supported Operating Systems	Windows 8.1 / 8 / 7 / Vista SP1 & SP2 / XP SP3 32-bit Mac OS X v10.6.8 or later
-----------------------------	--

Supported Mobile Systems	iOS (PIXMA Printing Solutions app, AirPrint) Android (PIXMA Printing Solutions app) Windows RT
Minimum System Requirements	Windows: Internet Explorer 8, internet connection or CD-ROM Mac: Safari 5 and internet connection Display: 1024 x 768 XGA
Software Included	MP Driver with Scanning Utility Quick Menu My Image Garden Easy-WebPrint EX (plug-in for IE8 or higher)

PHYSICAL FEATURES

[Back to Top](#)

Display Type & Size	6.2cm colour TFT display with Dual Function Panel
Display languages	English, German, French, Italian, Spanish, Dutch, Portuguese, Norwegian, Swedish, Danish, Finnish, Russian, Czech, Hungarian, Polish, Slovene, Turkish, Greek, Slovakian, Estonian, Latvian, Lithuanian, Ukrainian, Romanian, Bulgarian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Indonesian
Automatic Document Feeder	Up to 35-sheets, Auto 2-sided
Dimensions (W x D x H)	491 x 396 x 231mm
Weight	11.7kg
Power Source	AC 100-240V, 50/60Hz
Power Consumption	Standby: Approx. 1.0 W (USB connection to PC, scanning lamp off) Off: Approx. 0.4 W (USB connection to PC) Copying: Approx. 17 W ¹
Acoustic Noise Levels	Approx. 44.0 dB(A) ¹
Operating Temperature	15-30°C
Operating Humidity	5-95%RH (no dew condensation)
Duty Cycle	up to 12,000 pages / month
Print Resolution	¹ Ink droplets can be placed with a minimum pitch of 1/9600 inch.
Mono Document Print Speed	¹ Document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.
Colour Document Print Speed	¹ Document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.
Photo Print Speed	¹ Photo print speed is based on default driver setting using ISO/JIS-SCID N2 standard on Canon Photo Paper Plus Glossy II and does not take into account data processing time on host computer.
Scanner Resolution (Optical)	¹ Optical resolution is a measure of maximum hardware sampling resolution based on ISO 14473 standard. When scanning in high resolution, the scan size is restricted.

A4 Scan Speed	¹ Colour document scan speed is measured with ISO/IEC 24735 Annex C Test Chart A. Scan speed indicates the time measured between pressing the scan button of the scanner driver and the on-screen status display turns off.
Copy Speed Colour Document	¹ Colour document copy speed is measured based on average of sFCOT and sESAT in Performance Test of ISO/IEC 29183 standard.
Fax Speed	¹ Fax transmission speed is based on default setting using ITU-T No.1 chart for mono and Canon Colour Fax Test Sheet for colour. Actual transmission speed may vary depending on document complexity, fax settings at receiving end, and line conditions etc.
Wireless Connections	¹ Wi-Fi frequency band: 2.4GHz, Wi-Fi Security: WPA-PSK, WPA2-PSK, WEP, Administration password.
Applications Support	¹ PIXMA Printing Solutions is Canon's free application for smartphones and tablets. Not available in certain countries or regions.
Power Consumption	¹ When copying ISO/JIS-SCID N2 (printed by inkjet printer) on A4 size plain paper using default settings.
Acoustic Noise Levels	¹ When printing ISO/JIS-SCID N2 pattern on 10x15cm Photo Paper Plus Glossy II using default settings.