



tool black lacquered; handles with multi-component grips



**95 31 280**

**Model 95 31 280 :**

- fixed handle with support area for putting down the pliers when cutting
- suitable for aluminium sector cable up to 4 x 150 mm<sup>2</sup>






95 31 280: Large cutting capacity: maximum 52 mm dia. / 380 mm<sup>2</sup>



Ratchet principle and two-stage ratchet drive for easier cutting



95 31 250/280: fixed handle with support area as an aid to position the cutters on a flat surface

Article No.	EAN 4003773-	 Ø mm	 mm <sup>2</sup>	MCM	 mm
<a href="#">95 31 250</a>	043935	32	240	500	250
<a href="#">95 31 280</a>	043942	52	380	750	280
<a href="#">95 36 250</a>	026884	32	240	500	250
<a href="#">95 36 280</a>	026891	52	380	750	280