



"STYLE" refers to shape of antenna in series.

Item #	Style	Description	1-9	10-24	25-99	100+
--------	-------	-------------	-----	-------	-------	------

**2.4 GHz Mobile Mount Antennas - Built for Demanding Mobile Applications**

Our extensive line of magnetic mount and mast mount mobile Omnidirectional antennas are perfect for demanding mobile applications including law enforcement, construction vehicles, and mobile metering. Several styles are offered with many frequency and gain choices supporting IEEE 802.11b/g/n.

- All weather construction
- IEEE 802.11b/g/n
- Bluetooth® and WiFi
- Magnetic and mast mount options
- RoHS compliant

**Magnetic Mobile Mounts**

HMA6-RSP05	B	RP-SMA Jack to RP-SMA Plug, 5ft (1.5m) 100-Series	19.95	18.35	16.76	CALL
HMA6-RSP10	B	RP-SMA Jack to RP-SMA Plug, 10ft (3.0m) 100-Series	29.95	27.55	25.16	CALL
HMA6-RTPO5	B	RP-SMA Jack to RP-TNC Plug, 5ft (1.5m) 100-Series	19.95	18.35	16.76	CALL
HMA6-RTP10	B	RP-SMA Jack to RP-TNC Plug, 10ft (3.0m) 100-Series	29.95	27.55	25.16	CALL
HMA1-NFA10	C	NMO to N Female, 10ft (3.0m) 195-Series	24.95	22.95	20.96	CALL
HMA1-NMA10	C	NMO to N Male, 10ft (3.0m) 195-Series	24.95	22.95	20.96	CALL
HMA1-RSPA10	C	NMO to RP-SMA Plug, 10ft (3.0m) 195-Series	24.95	22.95	20.96	CALL
HMA1-RTPA10	C	NMO to RP-TNC Plug, 10ft (3.0m) 195-Series	24.95	22.95	20.96	CALL
HMA3-NFA10	D	N Female to N Female, 10ft (3.0m) 195-Series	27.95	25.71	23.48	CALL
HMA3-NMA10	D	N Female to N Male, 10ft (3.0m) 195-Series	27.95	25.71	23.48	CALL
HMA3-RSPA10	D	N Female to RP-SMA Plug, 10ft (3.0m) 195-Series	27.95	25.71	23.48	CALL
HMA3-RTPA10	D	N Female to RP-TNC Plug, 10ft (3.0m) 195-Series	27.95	25.71	23.48	CALL

**2.4 GHz Antennas with Magnetic Mobile Mounts**

HG2403MGU-NM	F	3 dBi, Dual Band, 10ft (3.0m) Cable with N Male Connector	39.95	36.75	33.56	CALL
HG2403MGU-RSP	F	3 dBi, Dual Band, 10ft (3.0m) Cable with RP-SMA Plug Connector	39.95	36.75	33.56	CALL
HG2403MGU-RTP	F	3 dBi, Dual Band, 10ft (3.0m) Cable with RP-TNC Plug Connector	39.95	36.75	33.56	CALL
HG2403MGURW-NM	G	3 dBi, White Radome, 10ft (3.0m) Cable with N Male Connector	42.95	39.51	36.08	CALL
HG2403MGURW-RSP	G	3 dBi, White Radome, 10ft (3.0m) Cable with RP-SMA Plug Connector	42.95	39.51	36.08	CALL
HG2403MGURW-RTP	G	3 dBi, White Radome, 10ft (3.0m) Cable with RP-TNC Plug Connector	42.95	39.51	36.08	CALL
HG2403MGURB-NM	G	3 dBi, Black Radome, 10ft (3.0m) Cable with N Male Connector	42.95	39.51	36.08	CALL
HG2403MGURB-RSP	G	3 dBi, Black Radome, 10ft (3.0m) Cable with RP-SMA Plug Connector	42.95	39.51	36.08	CALL
HG2403MGURB-RTP	G	3 dBi, Black Radome, 10ft (3.0m) Cable with RP-TNC Plug Connector	42.95	39.51	36.08	CALL
HG2405MGU-NM	E	5 dBi, 10ft (3.0m) Cable with N Male Connector	49.95	46.95	43.96	CALL
HG2405MGU-RSP	E	5 dBi, 10ft (3.0m) Cable with RP-SMA Plug Connector	49.95	46.95	43.96	CALL
HG2405MGU-RTP	E	5 dBi, 10ft (3.0m) Cable with RP-TNC Plug Connector	49.95	46.95	43.96	CALL
HG2409MGU-NF	I	8.5 dBi, 10ft (3.0m) Cable with N Female Connector	77.95	73.27	68.60	CALL
HG2409MGU-NM	I	8.5 dBi, 10ft (3.0m) Cable with N Male Connector	77.95	73.27	68.60	CALL
HG2409MGU-RSP	I	8.5 dBi, 10ft (3.0m) Cable with RP-SMA Plug Connector	77.95	73.27	68.60	CALL

**2.4 GHz Mobile Mount Antennas**

HG2403U-NMO	F	3 dBi, Dual Band, Integral NMO Connector	32.95	30.31	27.68	CALL
HG2403UR-NMOW	G	3 dBi, White Radome, Integral NMO Connector	30.95	28.47	26.00	CALL
HG2403UR-NMOB	G	3 dBi, Black Radome, Integral NMO Connector	30.95	28.47	26.00	CALL
HG2405U-NMO	E	5 dBi, Integral NMO Connector	22.95	21.11	19.28	CALL
HG2405UR-NMO	H	5 dBi, Black Radome, Flex-Base, Integral NMO Connector	94.95	87.35	79.76	CALL
HG2408UR-NM	H	8 dBi, Black Radome, Flex-Base, Integral N Male Connector	94.95	89.25	83.56	CALL
HG2409U	I	8.5 dBi, Integral N Male Connector	55.95	52.59	49.24	CALL

**700 - 2700 MHz DAS Ceiling Mount Antennas**

The HyperLink's high performance broadband/multi-band ceiling mount DAS antennas are designed to operate from 800 MHz to 3 GHz. These high performance antennas are specifically designed to distribute Cellular and WiFi signals throughout a building or area. The Multi-Band design of this antenna eliminates the need to purchase different antennas for each frequency.

HG2404CU-NF	L	800 MHz-3.0 GHz, 3.5 dBi, Ceiling Mount DAS Antenna, N Female Connector	24.95	23.45	21.96	CALL
HG2404CU-RSP	L	800 MHz-3.0 GHz, 3.5 dBi, Ceiling Mount DAS Antenna, RP-SMA Plug Connector	24.95	23.45	21.96	CALL
HG2404CU-RTP	L	800 MHz-3.0 GHz, 3.5 dBi, Ceiling Mount DAS Antenna, RP-TNC Plug Connector	24.95	23.45	21.96	CALL
HG27204CU-NF	L	700 MHz-3/4 dBi, Ceiling Mount DAS Antenna, N Female Connector	34.95	32.15	29.36	CALL
HG27204CU-RSP	L	700 MHz-3/4 dBi, Ceiling Mount DAS Antenna, RP-SMA Plug Connector	34.95	32.15	29.36	CALL
HG27204CU-RTP	L	700 MHz-3/4 dBi, Ceiling Mount DAS Antenna, RP-TNC Plug Connector	34.95	32.15	29.36	CALL

**2.4 GHz/2.4-5.8 GHz Ceiling Antennas - Indoor Single Band/Dual Band/MIMO Antennas**

L-com offers a number of Ceiling Antennas in 2.4 GHz and 2.4/5.8 GHz frequencies for many indoor applications. The coverage is 360° and operating with single feed (1 X 1) as well as the new MIMO Multiple feeds (3 X 3 and 6 X 6). MIMO antennas provide the user with a single antenna to couple with the many multiple feed wireless radios operating in 802.11a/b/g/n. The MIMO antennas provide spatial and frequency diversity to improve connectivity and data throughput for the user.

**2.4 GHz MIMO Spatial Diversity Ceiling Antennas**

HG2403-SDC-3NF	J	3 dBi, Spatial Diversity Ceiling Antenna, 3 N Female Connectors	55.95	53.71	51.47	CALL
HG2403-SDC-3NM	J	3 dBi, Spatial Diversity Ceiling Antenna, 3 N Male Connectors	55.95	53.71	51.47	CALL
HG2403-SDC-3RSP	J	3 dBi, Spatial Diversity Ceiling Antenna, 3 RP-SMA Plug Connectors	55.95	53.71	51.47	CALL
HG2403-SDC-3RTP	J	3 dBi, Spatial Diversity Ceiling Antenna, 3 RP-TNC Plug Connectors	55.95	53.71	51.47	CALL

**2.4/5.8 GHz Dual Band MIMO Spatial Diversity Ceiling Antennas**

HG2458-3SDC-3NF	J	3 dBi, Dual Band Spatial Diversity, 3 N Female Connectors	55.95	52.59	49.24	CALL
HG2458-4SDC-6NF	K	4 dBi, Dual Band Spatial Diversity, 6 N Female Connectors	83.95	78.91	73.88	CALL
HG2458-4SDC-6NM	K	4 dBi, Dual Band Spatial Diversity, 6 N Male Connectors	83.95	78.91	73.88	CALL
HG2458-4SDC-6RSP	K	4 dBi, Dual Band Spatial Diversity, 6 RP-SMA Plug Connectors	83.95	78.91	73.88	CALL
HG2458-4SDC-6RTP	K	4 dBi, Dual Band Spatial Diversity, 6 RP-TNC Plug Connectors	83.95	78.91	73.88	CALL

**2.4/5.8 GHz Dual Band Ceiling Antennas**

HG2458CU-NF	L	3 dBi, Dual Band Ceiling Antenna, N Female Connector	44.95	41.35	37.76	CALL
HG2458CU-RTP	L	3 dBi, Dual Band Ceiling Antenna, RP-TNC Plug Connector	44.95	41.35	37.76	CALL