



### PC/AT Modem Cables

Connect PC and AT compatibles to async modems or DCE devices.



Good

BC00301



Best

EVMBSM

#### Standard Modem Cables

- Fully molded hoods with thumbscrews for easy connection.
- Aluminum foil shield for noisy environments.
- FIDO PROTECTION®** — Lifetime

Item	Code	List Price
AT® Modem Cable, Standard, DB9 Female/DB25 Male, 9-Conductor, 28 AWG		
6-ft. (1.8-m)	BC00301	\$12.95
10-ft. (3.0-m)	BC00302	\$14.95
PC Modem Cable, Standard, DB25 Male/DB25 Female, 10-Conductor, 28 AWG		
6-ft. (1.8-m)	BC00401	\$12.95
10-ft. (3.0-m)	BC00402	\$14.95

#### Premium Modem Cables

- Nonmolded assemblies with removable hoods for easy repinning.
- Foil shield and drain wire for noisy environments.
- FIDO PROTECTION®** — Lifetime

Item	Code	List Price
AT Modem Cable, Premium, DB9 Female/DB25 Male, 9-Conductor, 24 AWG		
6-ft. (1.8-m)	EVMBMC-0006	\$17.95
10-ft. (3.0-m)	EVMBMC-0010	\$19.95
25-ft. (7.6-m)	EVMBMC-0025	\$23.95
50-ft. (15.2-m)	EVMBMC-0050	\$30.95
Custom Lengths	EVNBMC	\$16.15 + \$4.44/ft.
PC Modem Cable, Premium, DB25 Male/DB25 Female, 25-Conductor, 24 AWG		
6-ft. (1.8-m)	EVMBSM-0006	\$21.95
10-ft. (3.0-m)	EVMBSM-0010	\$25.95
25-ft. (7.6-m)	EVMBSM-0025	\$37.95
50-ft. (15.2-m)	EVMBSM-0050	\$56.95
Custom Lengths	EVNBSM	\$21.55 + \$7.66/ft.

### DB25 Serial Null-Modem Cable

Connect two serial devices configured as DTE or DCE async only.

- Connect computer to computer for file transfer through a serial port.
- Cross-pinned.
- Can be used for hardware flow-control or X-ON/X-OFF applications.
- FIDO PROTECTION®** — Lifetime



BC00502



Item	Code	List Price
DB25 Serial Null-Modem Cable		
DB25 Female/DB25 Female		
6-ft. (1.8-m)	BC00501	\$14.95
10-ft. (3.0-m)	BC00503	\$16.95
15-ft. (4.5-m)	BC00505	\$19.95
20-ft. (6.0-m)	BC00507	\$22.95
25-ft. (7.6-m)	BC00509	\$24.95
DB25 Male/DB25 Male		
6-ft. (1.8-m)	BC00502	\$14.95
10-ft. (3.0-m)	BC00504	\$16.95
15-ft. (4.5-m)	BC00506	\$19.95
20-ft. (6.0-m)	BC00508	\$22.95
25-ft. (7.6-m)	BC00510	\$24.95

### DB9 Serial Null-Modem Cable

Transfer files between AT computers.

- Ideal for AT to AT file transfers.
- Pins 2 and 3 are crossed for RS-232 standards compliance.
- Has 115-ohm nominal impedance at 1 MHz or above.
- FIDO PROTECTION®** — Lifetime



EYN257H



Item	Code	List Price
DB9 Serial Null-Modem Cable		
DB9 Male/DB9 Female		
6-ft. (1.8-m)	EYN257T-0006-MF	\$21.95
10-ft. (3.0-m)	EYN257T-0010-MF	\$23.95
15-ft. (4.5-m)	EYN257T-0015-MF	\$25.95
25-ft. (7.6-m)	EYN257H-0025-MF	\$28.95
50-ft. (15.2-m)	EYN257H-0050-MF	\$37.95
Custom Lengths	EYN257H	\$21.55 + \$3.33/ft.
DB9 Female/DB9 Female		
6-ft. (1.8-m)	EYN257T-0006-FF	\$21.95
10-ft. (3.0-m)	EYN257T-0010-FF	\$23.95
15-ft. (4.5-m)	EYN257H-0015-FF	\$25.95
25-ft. (7.6-m)	EYN257H-0025-FF	\$28.95
50-ft. (15.2-m)	EYN257H-0050-FF	\$37.95
Custom Lengths	EYN257H	\$21.55 + \$3.33/ft.

NOTE: Standard male/male versions are also in stock—just call!

### PC Data-Transfer Cables

The easy way to transfer data from your laptop or notebook.



BC01801

BC01802



- Transfer data quickly right from your laptop.
- Support for file-transfer software (DOS 6.0, LAPLINK, and more).
- FIDO PROTECTION®** — Lifetime

Item	Code	List Price
PC Data-Transfer Cables		
Parallel (DB25 Male/DB25 Male)		
6-ft. (1.8-m)	BC01801	\$11.95
Universal Serial (DB25 Female/DB9 Female to DB25 Female/DB9 Female)		
10-ft. (3.0-m)	BC01802	\$15.95