

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **50-57-9008**
Status: **Active**
Overview: SL™ Modular Connectors
Description: SL™ Crimp Housing, Single Row, Version A, Non-polarized, 8 Circuits

Documents:

3D Model	Product Specification PS-71851 (PDF)
Drawing (PDF)	Test Summary TS-70058-001 (PDF)
Product Specification PS-70058 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-70400 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>70066</u>
Application	Signal, Wire-to-Board
Comments	Version A
Overview	<u>SL™ Modular Connectors</u>
Product Name	SL™
UPC	800753629639

Physical

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Resin	Polyester Alloy
Net Weight	0.057/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40°C to +105°C

Electrical


Current - Maximum per Contact	3A
-------------------------------	----

Material Info

Old Part Number	70066-0007
-----------------	------------

Reference - Drawing Numbers

Product Specification	PS-70058, PS-70400, PS-71851
Sales Drawing	SD-70066-0001-0024
Test Summary	TS-70058-001

EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status Not Low-Halogen	China RoHS 
---	--

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

70066Series

Mates With

[42375](#) , [42377](#) , [70280](#) , [70287](#) , [71308](#) , [70543](#) , [70553](#)

Use With

SL™ Crimp Terminal [70058](#) , [71851](#)