



- **Black Box Products**

Cables > Copper Patch Cables

click photo to enlarge

Photo may show similar product

Other views



GigaBase 350 CAT5e Patch Cable (UTP), Snagless Boots, Crossover, 20-ft. (6.0-m), Yellow

The great choice for Gigabit crossover applications.

EVCRB84-0020

Extended Double Diamond™ Warranty Available (Lifetime)

Product Highlights

- Tested to 350 MHz.
- Meets or exceeds CAT5e T568B standards.
- Specially designed for use with other GigaBase components.
- Guaranteed for life!



- [Details](#)
- [Tech Specs](#)
- [Resources](#)
- [Warranty](#)
- [Similar Products](#)

Description

GigaBase 350 CAT5e Patch Cable (UTP), Snagless Boots, Crossover, 20-ft. (6.0-m), Yellow

Quick Facts

- Tested to 350 MHz.
- Meets or exceeds CAT5e T568B standards.
- Specially designed for use with other GigaBase components.
- Guaranteed for life!

Further Details

- Improved near-end crosstalk (NEXT) compared to standard CAT5 cable.
- Superior construction offers significant headroom.
- Stranded conductors for short runs.
- Tuned-plug design maintains a tighter twist and reduces noise.
- Enhanced performance parameters and electrical characteristics.
- Gold-plated contacts are designed for an insertion/extraction life of 1000 cycles.
- These patch cables have four pairs, 24 AWG construction, RJ-45 connectors, and a PVC jacket.
- Quantity discounts and 25-packs are available upon request. To order, contact our FREE Tech Support.