

LC1F115G6

Contacteur (TeSys F) Non-Reversing, 115A(AC3)
200A(AC1), 3-Pole

Technical Characteristics

Contacteur Type	Non-Reversing
Terminal Type	Screw Clamp
Type	TeSys F
Inductive Amperes (AC3)	115A
Resistive Amperes (AC1)	200A
Horsepower Rating (3-Phase)	30HP@200VAC - 40HP@230VAC - 75HP@460VAC - 100HP@575VAC
Marketing Trade Name	TeSys
Maximum Voltage Rating	600VAC
Number of Poles	3-Pole
Coil Voltage	120VAC@60Hz

Shipping and Ordering

Category	22336 - Contactors, AC, Open, Non-Reversing, F-Line
GTIN	00785901079781
Package Quantity	1
Weight	8.9 lbs.
Country of Origin	CZ

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.