

MECHANICAL DETAILS

Shell Style Model BRE* : Blanking cap for fixed receptacle with silicone o-ring


Keying No keying

Housing Material Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces


Cable Fixing 0 - 0 mm

Variant 2 :

	Col	Col	Col	Col	Col	Col	Col	Col
Mm.								
In.								



Available Download

 unipole_multipole.pdf

PERFORMANCE DETAIL

Insert :

Insulator

Insulator



OTHER CHARACTERISTICS

Endurance (Shell) Endurance (Shell):

Temp (min) -55°C

Temp (max) +200°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]

Salt Spray >144 hr







Climatical 50/175/21

Shielding (min): 95 dB (10 MHz)

Shielding (min): 80 dB (1 GHz)

IP Rating 68

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)