


MECHANICAL DETAILS

Shell Style Model	FG* : Straight plug
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Housing Material	Environment friendly aluminium (nickel plated, anthracite color) shell and nut, other pieces beryllium copper
Cable Fixing	0 - 0 mm

Variant 2 :

	A	B	L	M
Mm.	12	9	27.5	18
In.	0.47	0.35	1.08	0.71



Available Download

 [f_series.pdf](#)

PERFORMANCE DETAIL

Insert	0F.305 : 5 Low Voltage
Insulator	L: PEEK
Specifications	
Contact Type:	Crimp
Max. Matings:	5000
Contact	22 N
Contact Dia.:	0.7 mm (0.028in)
Bucket Dia.:	0.8 mm (0.031in)
Min. Conductor:	0.14 mm ² (AWG 26)
Max. Conductor:	0.34 mm ² (AWG 22)
R (max):	6.1 mOhm
Positioner:	DCE.91.070.BVC









OTHER CHARACTERISTICS

Endurance (Shell)	Endurance (Shell):
Temp (min)	-15°C
Temp (max)	+200°C
Humidity (max):	<=95% [at 60 deg C /140 F]
Vibration:	15 g [10 Hz - 2000 Hz]
Shock Resistance:	100 g [6 ms]
Climatical	15/200/21 (Aluminium shell)
IP Rating	67



Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)