

CONTROL PRODUCTS

Piezo switches, Plastic, RGB LED Illuminated, 26mm

Plastic piezo switches offering rugged, sealed tamper and vandal proof solid state switching. Exceptional durability and reliability. Fitted with red, green and blue LED's for illumination.

- 26mm diameter actuator
- 22.5mm diameter mounting hole
- Normally open, momentary action
- Make impulse time of 125-300 msec
- Recessed face
- Wire termination
- IP68 Sealed
- Available in 12V and 24V LED's

CPS221F-PLWH-12RGB



SPECIFICATIONS

Operating voltage:	1-24V AC/DC	
Switching current	0.2A max	
Actuation force	3-5N	
Operating temperature	from -20°C to +70°C	
LED Operating voltage	12V DC max OR 24V DC max	
LED max current consumption:	(12V)	(24V)
Red	18mA	18mA
Green	9mA	9mA
Blue	27mA	16mA
Ingress Protection	IP69	
Lifetime	50 million operations	
Material	POM	

PART NO.	LED VOLTAGE
CPS221F-PLWH-12RGB	12V DC
CPS221F-PLWH-24RGB	24V DC

