



# GMA.0B.040.DJ

## MECHANICAL DETAILS

**Shell Style Model** GMA\* : Bend relief Yellow


**Keying** No keying

**Housing Material** Thermoplastic polyurethane elastomer(Desmopan 786)

**Cable Fixing** 4 - 4.4 mm

**Variant 2** J : Yellow

	Col	Col	Col	Col	Col	Col	Col	Col
Mm.								
In.								



## PERFORMANCE DETAIL

**Insert** :

**Insulator** J: PEEK/PEEK

**Insulator** J: PEEK/PEEK

## OTHER CHARACTERISTICS

**Shell Style/Model** Libellé

**Temp (min)** -40°C

**Temp (max)** +80°C

**IP Rating** 0

