



# GMA.0B.045.RB

## MECHANICAL DETAILS

**Shell Style Model** GMA\* : Bend relief White


**Keying** No keying

**Housing Material** Silicone elastomer VMQ

**Cable Fixing** 4.5 - 5.2 mm

**Variant 2** V : White

	Col	Col	Col	Col	Col	Col	Col	Col
Mm.								
In.								



## OTHER CHARACTERISTICS

**Shell Style/Model** Libellé

**Temp (min)** -60°C

**Temp (max)** +200°C

**Temperature** +140°C

**IP Rating** 0