

Han D HMC male contact Au AWG 16



| Features | |
|---------------------------------|------------------------------|
| Gender: | male |
| RoHS conformity: | Yes |
| Type of contact: | Crimp contact |
| Series: | Han D® HMC |
| Connection data | |
| Contact resistance: | ≤ 3 mOhm |
| Wire gauge: | 1.5 mm ² |
| Wire gauge AWG: | AWG 16 |
| Stripping length: | 8 mm |
| Wire gauge AWG, min.: | AWG 26 |
| Wire gauge AWG, max.: | AWG 14 |
| Material properties | |
| Material, contact: | copper alloy |
| Surface, contacts: | HMC gold plated contacts |
| Dimensions and weight | |
| Net Weight: | 0.62 g |
| Norms and specifications | |
| Specification: | DIN EN 60 664-1DIN EN 61 984 |
| Supplementals | |
| Diameter of drilling hole: | 1.75 mm |