

Kit P/N:GRM18-KIT-E [0603 Class 1 & 2 series]

Wallet

No.	Murata Global P/N	Size (EIA)	TC	WV	Cap.	Cap. Tol.	QTY
1	GRM1885C1H100JA01	0603	C0G	50V	10pF	±5%	100
2	GRM1885C1H120JA01	0603	C0G	50V	12pF	±5%	20
3	GRM1885C1H150JA01	0603	C0G	50V	15pF	±5%	20
4	GRM1885C1H180JA01	0603	C0G	50V	18pF	±5%	20
5	GRM1885C1H220JA01	0603	C0G	50V	22pF	±5%	20
6	GRM1885C1H270JA01	0603	C0G	50V	27pF	±5%	20
7	GRM1885C1H330JA01	0603	C0G	50V	33pF	±5%	20
8	GRM1885C1H390JA01	0603	C0G	50V	39pF	±5%	20
9	GRM1885C1H470JA01	0603	C0G	50V	47pF	±5%	20
10	GRM1885C1H560JA01	0603	C0G	50V	56pF	±5%	20
11	GRM1885C1H680JA01	0603	C0G	50V	68pF	±5%	20
12	GRM1885C1H820JA01	0603	C0G	50V	82pF	±5%	20
13	GRM1885C1H101JA01	0603	C0G	50V	100pF	±5%	100
14	GRM1885C1H121JA01	0603	C0G	50V	120pF	±5%	20
15	GRM1885C1H151JA01	0603	C0G	50V	150pF	±5%	20
16	GRM1885C1H181JA01	0603	C0G	50V	180pF	±5%	20
17	GRM1885C1H221JA01	0603	C0G	50V	220pF	±5%	20
18	GRM1885C1H271JA01	0603	C0G	50V	270pF	±5%	20
19	GRM1885C1H331JA01	0603	C0G	50V	330pF	±5%	20
20	GRM1885C1H391JA01	0603	C0G	50V	390pF	±5%	20
21	GRM1885C1H471JA01	0603	C0G	50V	470pF	±5%	20
22	GRM1885C1H561JA01	0603	C0G	50V	560pF	±5%	20
23	GRM1885C1H681JA01	0603	C0G	50V	680pF	±5%	20
24	GRM1885C1H821JA01	0603	C0G	50V	820pF	±5%	20
25	GRM1885C1H102JA01	0603	C0G	50V	1000pF	±5%	100
26	GRM1885C1H122JA01	0603	C0G	50V	1200pF	±5%	20
27	GRM1885C1H152JA01	0603	C0G	50V	1500pF	±5%	20

No.	Murata Global P/N	Size (EIA)	TC	WV	Cap.	Cap. Tol.	QTY
28	GRM1885C1H182JA01	0603	C0G	50V	1800pF	±5%	20
29	GRM1885C1H222JA01	0603	C0G	50V	2200pF	±5%	20
30	GRM1885C1H272JA01	0603	C0G	50V	2700pF	±5%	20
31	GRM1885C1H332JA01	0603	C0G	50V	3300pF	±5%	20
32	GRM1885C1H392JA01	0603	C0G	50V	3900pF	±5%	20
33	GRM1885C1H472JA01	0603	C0G	50V	4700pF	±5%	20
34	GRM1885C1H562JA01	0603	C0G	50V	5600pF	±5%	20
35	GRM1885C1H682JA01	0603	C0G	50V	6800pF	±5%	20
36	GRM1885C1H822JA01	0603	C0G	50V	8200pF	±5%	20
37	GRM1885C1H103JA01	0603	C0G	50V	0.01μF	±5%	100
38	GRM188R71H103KA01	0603	X7R	50V	0.01μF	±10%	100
39	GRM188R71H223KA01	0603	X7R	50V	0.022μF	±10%	20
40	GRM188R71H473KA61	0603	X7R	50V	0.047μF	±10%	20
41	GRM188R71H104KA93	0603	X7R	50V	0.1μF	±10%	100
42	GRM188R71E224KA88	0603	X7R	25V	0.22μF	±10%	20
43	GRM188R71C474KA88	0603	X7R	16V	0.47μF	±10%	20
44	GRM188R61E105KA12	0603	X5R	25V	1μF	±10%	100
45	GRM188R61A105KA61	0603	X5R	10V	1μF	±10%	100
46	GRM188R61E225KA12	0603	X5R	25V	2.2μF	±10%	20
47	GRM188R61A475ME15	0603	X5R	10V	4.7μF	±20%	20
48	GRM188R61E475KE11	0603	X5R	25V	4.7μF	±10%	20
49	GRM188R60J106ME47	0603	X5R	6.3V	10μF	±20%	100
50	GRM188D71A106MA73	0603	X7T	10V	10μF	±20%	100
51	GRM188R61E106MA73	0603	X5R	25V	10μF	±20%	100
52	GRM188R60J226MEA0	0603	X5R	6.3V	22μF	±20%	20
53	GRM188R61A226ME15	0603	X5R	10V	22μF	±20%	20
54	GRM188R60J476ME15	0603	X5R	6.3V	47μF	±20%	20

Effective October 2014

Subject to change without notice.

For the latest product information please check our website or contact you local Murata Sales Office

<http://www.murata.com/>

